







P.C.B. HOLE DRILLINGS (P.C.B. TOP SIDE)



Directive 2002/95/EC RoHS compliant



NOTES:

1. METAL SHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; BLACK
3. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
4. PLASTIC BRACKETS: PBT GF UL 94 V-0; BLACK
5. THREADED LOCKS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. FIXING-PLATE: PBT GF UL 94 V-0; BLACK
7. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
8. CONNECTOR IS PART MARKED: **163A19129X CONEC ABC**

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale:		2:1 (5:1)	
								material:		see notes	
						date	name		title: D-SUB MALE 90° 9pos. SOLDER PIN ANGLED 0.590inch threaded lock, plastic bracket, fixing plate		
					drawn	02.12.10	Schmidt				
					appd.	08.12.10	Fischer				
					norm						
					d-old			dwg no:		DIN-A3	
								16K1A2736		sh: 1	
	a	Origin									
	rev.	description	date	name				part no:		163A19129X	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[163A19129X](#)