




EC6C SERIES

25 - 30WATT 2:1 INPUT DC-DC CONVERTERS



FEATURES

- * 25-30W Isolated Output
- * 2" X 2" Six-Sided Shield Metal Case
- * 2:1 Input Range
- * Regulated Outputs
- * Efficiency to 88%
- * Remote ON/OFF Control
- * CE Mark Meets 2004/108/EC
- * UL60950-1 Approval



章 節	C-7
頁 次	1-1

MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT		INPUT CURRENT		% EFF.	Capacitor Load max.
			MIN.	MAX.	NO LOAD	FULL LOAD		
EC6C01	9-18VDC	5VDC	0mA	5000 mA	30 mA	2675 mA	84	5000uF
EC6C02	9-18VDC	12VDC	0mA	2500 mA	30 mA	3050 mA	88	2500uF
EC6C03	9-18VDC	15VDC	0mA	2000 mA	30 mA	3050 mA	88	2000uF
EC6C04	9-18VDC	±5VDC	±0mA	±2500 mA	35 mA	2675 mA	83	2500uF
EC6C05	9-18VDC	±12VDC	±0mA	±1250 mA	35 mA	3050 mA	88	1250uF
EC6C06	9-18VDC	±15VDC	±0mA	±1000 mA	35 mA	3050 mA	87	1000uF
EC6C07	9-18VDC	5/±12VDC	500/±100 mA	3500/±310 mA	35 mA	2640 mA	81	T.B.D
EC6C08	9-18VDC	5/±15VDC	500/±100 mA	3500/±250 mA	35 mA	2640 mA	82	T.B.D
EC6C09	9-18VDC	3.3VDC	0mA	5000 mA	30 mA	1860 mA	80	5000uF
EC6C11	18-36VDC	5VDC	0mA	5000 mA	30 mA	1336 mA	83	5000uF
EC6C12	18-36VDC	12VDC	0mA	2500 mA	30 mA	1525 mA	87	2500uF
EC6C13	18-36VDC	15VDC	0mA	2000 mA	30 mA	1525 mA	87	2000uF
EC6C14	18-36VDC	±5VDC	±0mA	±2500 mA	30 mA	1336 mA	82	2500uF
EC6C15	18-36VDC	±12VDC	±0mA	±1250 mA	30 mA	1470 mA	87	1250uF
EC6C16	18-36VDC	±15VDC	±0mA	±1000 mA	30 mA	1470 mA	86	1000uF
EC6C17	18-36VDC	5/±12VDC	500/±100 mA	3500/±310 mA	30 mA	1320 mA	82	T.B.D
EC6C18	18-36VDC	5/±15VDC	500/±100 mA	3500/±250 mA	30 mA	1320 mA	82	T.B.D
EC6C19	18-36VDC	3.3VDC	0mA	5000 mA	30 mA	920 mA	79	5000uF
EC6C21	36-72VDC	5VDC	0mA	5000 mA	20 mA	660 mA	83	5000uF
EC6C22	36-72VDC	12VDC	0mA	2500 mA	20 mA	765 mA	87	2500uF
EC6C23	36-72VDC	15VDC	0mA	2000 mA	20 mA	765 mA	87	2000uF
EC6C24	36-72VDC	±5VDC	±0mA	±2500 mA	25 mA	660 mA	82	2500uF
EC6C25	36-72VDC	±12VDC	±0mA	±1250 mA	25 mA	735 mA	87	1250uF
EC6C26	36-72VDC	±15VDC	±0mA	±1000 mA	25 mA	735 mA	87	470uF
EC6C27	36-72VDC	5/±12VDC	500/±100 mA	3500/±310 mA	25 mA	655 mA	83	T.B.D
EC6C28	36-72VDC	5/±15VDC	500/±100 mA	3500/±250 mA	25 mA	655 mA	82	T.B.D
EC6C29	36-72VDC	3.3VDC	0mA	5000 mA	20 mA	460 mA	79	5000uF

NOTE: 1. Nominal Input Voltage 12, 24 or 48VDC

SPECIFICATIONS

All Specifications Typical At Nominal Line, Full Load, and 25°C Unless Otherwise Noted

INPUT SPECIFICATIONS:

Input Voltage Range	12V	9 – 18V
	24V	18 – 36V
	48V	36 – 72V
Input Surge Voltage (100ms max.)	12V	25Vdc max.
	24V	50Vdc max.
	48V	100Vdc max.
Input Filter	Pi Type	

OUTPUT SPECIFICATIONS:

Voltage Accuracy	
Single Output	±2.0% max.
Dual +Output	±2.0% max.
Dual – Output	±3.0% max.
Triple, 5V	±2.0% max.
12V/15V	±5.0% max.
Voltage Balance (Dual)	±1.0% max.
Transient Response	
Single 25% Step Load Change	<500us
Dual FL-1/2L±1% Error Band	<500us
External Trim Adj. Range	±10%
Ripple and Noise, 20MHz BW	10mV RMS. max., 75mV p-p max.
Temperature Coefficient	±0.02%/°C
Short Circuit Protection	Continuous
Line Regulation Single/Dual (note 1)	±0.5% max.
Triple	±1.0% max.
Load Regulation Single/Dual (note 2)	±1.0% max.
Triple	±5.0% max.
Start up time	900ms typ.

GENERAL SPECIFICATIONS:

Efficiency	See Table
Isolation Voltage	500 VDC min.
Isolation Resistance	10 ⁹ ohms
Isolation Capacitance	500pF typ.
Switching Frequency	300KHz typ.
Case Grounding	Connected to Output Common
Operating Ambient Temperature Range	-25°C to +71°C
De-rating, Above 60°C	Linearly to Zero power at 100°C
Case Temperature (note 3)	100°C max.
Cooling	Natural Convection
Storage Temperature Range	-55°C to +105°C
Humidity	95% RH max. Non condensing
MTBF	MIL-STD-217F, GB, 25°C, Full Load 900Khrs typ.
EMI/RFI	Six-Sided Continuous Shield
Dimensions	2.00×2.00×0.40 inches (50.8×50.8×10.2mm)
Case Material	Black Coated Copper With Non-Conductive Base
Weight	65g

NOTE:


1. Measured From High Line to Low Line
2. Measured From Full Load to 1/4 Full Load
3. Maximum case temperature under any operating condition should not be exceeded 100°C

Output (Pin No.)	Voltage	Amperes	
		Min. (2)	Nom.
7	+5	0.50	3.5
8 & 5	+12 & -12	0.10	0.31
8 & 5	+15 & -15	0.10	0.25

NOTE:


1. Maximum total power from all outputs is limited to 25 watts but no output should be allowed to exceed its maximum current
2. Minimum current on each output is required to maintain specified regulation

Typical Derating curve for Natural Convection



Case C Dimensions:

All Dimensions In Inches(mm)
 Tolerances Inches: X.XX= ±0.04, X.XXX= ±0.010
 Millimeters: X.X= ±1.0, X.XX=±0.25




Pin	Single	Dual	Triple
1. Remote On/Off Control			
2.	No Pin	No Pin	No Pin
3.	-Vin	-Vin	-Vin
4.	+Vin	+Vin	+Vin
5.	Trim	Trim	-Aux. Out
6.	-Vout	-Vout	Common
7.	+Vout	Common	+5Vout
8.	No Pin	+Vout	+Aux. Out

Logic Compatibility	CMOS or Open Collector TTL
Ec-On	>+5.5 VDC to 75Vdc or Open Circuit
Ec-Off	<1.8 VDC
Shutdown Idle Current	10mA
Control Common	Referenced to Input Minus

EXTERNAL OUTPUT TRIM

Output may optionally be externally trimmed (±10%) with a fixed resistor or an external trimpot as shown.



章節	C-7
頁次	1-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[EC6C04](#) [EC6C19](#) [EC6C14](#) [EC6C29](#) [EC6C24](#) [EC6C01](#) [EC6C02](#) [EC6C03](#) [EC6C05](#) [EC6C06](#) [EC6C07](#) [EC6C08](#)
[EC6C09](#) [EC6C11](#) [EC6C12](#) [EC6C13](#) [EC6C15](#) [EC6C16](#) [EC6C17](#) [EC6C18](#) [EC6C21](#) [EC6C22](#) [EC6C23](#) [EC6C25](#)
[EC6C26](#) [EC6C27](#) [EC6C28](#)