






NOTES:

1. METAL SHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATOR: PBT GF UL 94 V-0, BLACK
3. HIGH POWER CONTACTS 10A: COPPER ALLOY
PLATING, MATING AREA: GOLD FLASH over NICKEL
PLATING, TERMINATION SIDE: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 16-20
4. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
5. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. CAPACITANCE: 47 nF ± 20%
7. DIELECTRIC WITHSTANDING VOLTAGE: 707 VDC
8. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
9. CONNECTOR IS PART MARKED: 3F3SSA22S41A30X CONEC ABC

SOLDER INSTRUCTION:

1. THE WIRE HAVE TO BE PRETINNED
2. SOLDER TEMPERATURE max. 350°C
3. SOLDER TIME max. 15s

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (5:1)		
							material: SEE NOTES		
				date		name		title: D-SUB FILTER COMB. FEMALE 3W3S SOLDER CUP with threaded insert	
				drawn	14.07.15	Henneboel			
appd.	14.07.15	Lehmenkühler							
norm									
d-old				dwg no:		DIN-A3			
a	Original					24K1A1609			
rev.	description	date	name			sh: 1			
						part no: 3F3SSA22S41A30X			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

3F3SSA22S41A30X