



HEAT SINKS



HALF BRICK CASE HEATSINK


All Dimensions In mm

Longitudinal Fins Model No. :M-C308




Rca: 3.9°C/W (typ.), At natural convection
1.74°C/W (typ.), At 100LFM
1.33°C/W (typ.), At 200LFM
1.12°C/W (typ.), At 300LFM
0.97°C/W (typ.), At 400LFM

Transverse Fins Model No. :M-C091



Rca: 4.7°C/W (typ.), At natural convection
2.89°C/W (typ.), At 100LFM
2.30°C/W (typ.), At 200LFM
1.88°C/W (typ.), At 300LFM
1.59°C/W (typ.), At 400LFM

Transverse Fins Model No. :M-C092




Rca: 3°C/W (typ.), At natural convection
1.44°C/W (typ.), At 100LFM
1.17°C/W (typ.), At 200LFM
1.04°C/W (typ.), At 300LFM
0.95°C/W (typ.), At 400LFM

QUARTER BRICK CASE HEATSINK


All Dimensions In mm

Longitudinal Fins Model No. :M-C448 Thermal Pad: SZ56.9x35x0.25mm Screw: SMP+SW M3x8L



Rca: 5.61°C/W (typ.), At natural convection
4.01°C/W (typ.), At 100LFM
3.39°C/W (typ.), At 200LFM
2.86°C/W (typ.), At 300LFM
2.49°C/W (typ.), At 400LFM


Transverse Fins Model No. :M-C421 Thermal Pad: SZ56.9x35x0.25mm Screw: SMP+SW M3x8L



Rca: 4.78°C/W (typ.), At natural convection
2.44°C/W (typ.), At 100LFM
2.06°C/W (typ.), At 200LFM
1.76°C/W (typ.), At 300LFM
1.58°C/W (typ.), At 400LFM


HEAT SINK

Transverse Fins
Model No. :M-B012



Thermal Resistance: 2.07°C/W (typ.), At natural convection

HEAT SINK



Thermal Pad: SZ56.9x60x0.25mm
Screw: SMP+SW M3x8L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[M-B012](#) [M-C421](#) [M-C448](#)