



NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; BLACK
3. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
4. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
5. MAXIMUM TORQUE VALUE FOR THRED: 6 in.LB
6. CONNECTOR IS PART MARKED: DSS1XPXXG03X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (5:1)				
							material: SEE NOTES				
								date	name	title: D-SUB MALE 9pos. CRIMP STYLE with threaded insert	
								drawn 23.03.11	Henneboel		
								appd. 23.03.11	Fischer		
								norm			
								d-old			
a	Original					dwg no: 16K1A2805		DIN-A3			
rev.	description	date	name			part no: DSS1XPXXG03X		sh: 1			

CONEC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

DSS1XPXXG03X