



S E R I E S

EC4A

5-6 WATT WIDE INPUT DC-DC CONVERTERS



Features

- 5-6 W Isolated Output
- 24-Pin DIP Package
- Efficiency to 82%
- 2:1 Input Range
- Regulated Outputs
- Pi Input Filter
- Continuous Short Circuit Protection

MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT	INPUT CURRENT NO LOAD	INPUT CURRENT FULL LOAD	% EFF.	CASE
EC4A01	9-18 VDC	5 VDC	1000 mA	7.5 mA	545 mA	76	A
EC4A02		12 VDC	470 mA	7.5 mA	585 mA	80	
EC4A03		15 VDC	400 mA	7.5 mA	625 mA	80	
EC4A04		±12 VDC	±230 mA	12 mA	575 mA	80	
EC4A05		±15 VDC	±190 mA	12 mA	590 mA	80	
EC4A06		±5 VDC	±500 mA	12 mA	545 mA	76	
EC4A07		3.3 VDC	1000 mA	7.5 mA	393 mA	70	
EC4A11	18-36 VDC	5 VDC	1000 mA	5 mA	265 mA	78	A
EC4A12		12 VDC	470 mA	5 mA	285 mA	82	
EC4A13		15 VDC	400 mA	5 mA	305 mA	82	
EC4A14		±12 VDC	±230 mA	7.5 mA	285 mA	81	
EC4A15		±15 VDC	±190 mA	7.5 mA	295 mA	81	
EC4A16		±5 VDC	±500 mA	7.5 mA	265 mA	78	
EC4A17		3.3 VDC	1000 mA	5 mA	197 mA	70	
EC4A21	36-72 VDC	5 VDC	1000 mA	2 mA	133 mA	78	A
EC4A22		12 VDC	470 mA	2 mA	145 mA	81	
EC4A23		15 VDC	400 mA	2 mA	154 mA	81	
EC4A24		±12 VDC	±230 mA	3 mA	142 mA	81	
EC4A25		±15 VDC	±190 mA	3 mA	147 mA	81	
EC4A26		±5 VDC	±500 mA	3 mA	133 mA	78	
EC4A27		3.3 VDC	1000 mA	2 mA	98 mA	70	

NOTE: 1. Nominal Input Voltage 12, 24 or 48 VDC

Specifications

INPUT SPECIFICATIONS:

Input Voltage Range.....	12V.....	9-18V
	24V.....	18-36V
	48V.....	36-72V
Input Filter.....		PI Type

OUTPUT SPECIFICATIONS:

Voltage Accuracy.....		±2.0% max.
Voltage Balance (Dual).....		±1.0% max.
Temperature Coefficient.....		±0.05%/°C
Ripple and Noise, 20MHz BW.....	3.3V/5V.....	100mV p-p max.
	12V/15V.....	1% p-p max.
Short Circuit Protection.....		Continuous
Line Regulation, Single/Dual¹.....		± 0.5%
Load Regulation, Single².....		± 0.5%
	Dual³.....	± 1.0%

GENERAL SPECIFICATIONS:

Efficiency.....		See Table
Isolation Resistance.....		10⁹ohms
Switching Frequency.....		100KHz, min
Operating Temperature Range.....		-25°C to + 71°C
Case Temperature (Plastic case).....		95°C max.
	(Copper case).....	100°C max.
Cooling.....		Free-Air Convection
Storage Temperature Range.....		-40°C to + 100°C
Dimensions.....		1.25 x 0.8 x 0.4 inches (31.8 x 20.3 x 10.2mm)
Weight.....		12.5g

ISOLATION VOLTAGE:

500 VDC min.....		Standard Models
3K VDC min⁴.....		Suffix "H" Models

CASE MATERIAL:


Standard Models.....		Non-Conductive Black Plastic
Suffix "M" Models⁵.....		Black Coated Copper with Non-Conductive Base

NOTE:

1. Measured From High Line to Low Line
2. Measured From Full Load to 10% Load
3. Measured From Full Load to 1/4 Load
4. Non-Conductive Black Plastic Only
5. Suffix "HM" 1.5K VDC Instead of 3K VDC Isolation

CASE A

NOTE: Pin Size is 0.02" Inch (0.5mm) DIA
All Dimensions In Inches(mm)
Tolerance .xx= ±.02, .xxx= ±.010



PIN CONNECTION					
500 VDC			1.5K & 3K VDC		
Pin	Single Output	Dual Output	Pin	Single Output	Dual Output
1	+V Input	+V Input	1	NP	NP
2	NC	-V Output	2	-V Input	-V Input
3	NC	Common	3	-V Input	-V Input
9	NP	NP	9	NC	Common
10	-V Output	Common	10	NC	NC
11	+V Output	+V Output	11	NC	-V Output
12	-V Input	-V Input	12	NP	NP
13	-V Input	-V Input	13	NP	NP
14	+V Output	+V Output	14	+V Output	+V Output
15	-V Output	Common	15	NC	NC
16	NP	NP	16	-V Output	Common
22	NC	Common	22	+V Input	+V Input
23	NC	-V Output	23	+V Input	+V Input
24	+V Input	+V Input	24	NP	NP

*NP-NO PIN

*NC-NO CONNECTION WITH PIN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[EC4A21M](#)