

IES-150B



IES-150B

► Industrial 5-port mini type Unmanaged Ethernet Switch with 5x10/100Base-T(X)

Features

- Support 5 ports 10/100 Base-T(X)
- Support auto-negotiation and auto-MDI/MID-X
- Support Store and forward transmission
- Support flow control
- Compact size for easily installation
- Rigid IP-30 housing design
- DIN-rail and wall mounting enable



Introduction

IES-150B is unmanaged Ethernet Switch with 5x10/100Base-T(X) ports and extended operating temperature range from -40°C to 75°C for the harsh environments. The enclosure designed with compact size and a robust housing; it can help you to easily installed.

Power consumption (Typ.)	<3Watts, 12-48VDC: 0.10A-0.04A, 24VAC (50/60Hz) 0.10A
Overload current protection	Present
Reverse Polarity Protection	Present
Physical Characteristic	
Enclosure	IP-30 Metal
Dimension (W x D x H)	26.1 (W) x 70 (D) x 95 (H)mm 1.027 (W) x 2.755 (D) x 3.74 (H) inch
Weight (g)	205 g
Hardware Version	V3.0
Environmental	
Storage Temperature	-40 to 85°C (-40 to 185°F)
Operating Temperature	-40 to 75°C (-40 to 167°F)
Operating Humidity	5% to 95% Non-condensing
Regulatory approvals	
EMC	CE EMC (EN 55024, EN 55032), FCC Part 15 B
EMI	EN 55032, CISPR32, EN 61000-3-2, EN 61000-3-3, FCC Part 15 B class A
EMS	EN 55024 (IEC/EN 61000-4-2 (ESD: Contact 4KV, Air 8KV), IEC/EN 61000-4-3 (RS: 3V), IEC/EN 61000-4-4 (EFT Power 0.5KV, Signal 0.5KV), IEC/EN 61000-4-5 (Surge: Power 0.5KV, Signal 1KV), IEC/EN 61000-4-6 (CS: 3V), IEC/EN 61000-4-8(PFME), IEC/EN 61000-4-11 (DIP))
Shock	IEC60068-2-27
Free Fall	IEC60068-2-31
Vibration	IEC60068-2-6
Safety	IEC 60950-1, UL 60950-1, EN 60950-1 (LVD), UL61010-1, UL61010-2-201
Others	E-MARK
MTBF	2638236hrs
Warranty	5 years

Ordering Information

IES-1 **A** **B**



Code Definition	10/100Base-T(X) Port Number	Additional Port Number
Option	- 5: 5 ports	- 0: 0 port
Available Model	Model Name	Description
	IES-150B	Industrial 5-port mini type unmanaged Ethernet switch with 5x10/100Base-T(X)
Packing List - IES-150B x 1 - DIN-Rail Kit x 1 - Wall-mount Kit x 2 - Quick Installation Guide x 1		Optional Accessories - DR/SDR/DRP Series DIN-Rail power supply - PAE-121000, 12VDC/1000mA 12W Power Adapter with universal 100 to 240VAC input, EU plug. - PAA-121000, 12VDC/1000mA 12W Power Adapter with universal 100 to 240VAC input, US plug.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ORing:](#)

[IES-150B](#)