


TYPE 6

ICE-DB-T6R

Baseboard for COM Express Type 6 Module COM.0 Rev. 2.1
(for ICE-ULT3, ICE-QM871 & ICE-BT-T6)


Features

- ATX form factor baseboard for COM.0 Rev. 2.1, pin-out Type 6
- Support one PCIe x16, one PCIe x4, five PCIe x1, two PCIe Mini
- Support PICMG EAPI R1.0

Specifications

- ◆ Form Factor
 - ATX form factor baseboard
- ◆ CPU
 - Supports COM Express Compact/Mini module using connector pin out Type 6
- ◆ Display Interfaces
 - 1 x DisplayPort connectors
 - 1 x LVDS 18/24-bit single or dual-channel (with PWM back light controller)
 - 1 x VGA
 - 2 x DisplayPort pin-header
- ◆ Audio
 - Realtek ALC662 HD Audio codec (Line-in, Line-out, Mic)
- ◆ Expansion
 - 1 x LPC
 - 1 x PCIe x16
 - 1 x PCIe x4
 - 5 x PCIe x1
 - 2 x PCIe Mini (MINIPCI-E with mSATA support, colay with SATA_4)
- ◆ Internal I/O Interface
 - 1 x PS2 KB/MS
 - 4 x SATA port
 - 1 x SD card socket
- ◆ External I/O Interface
 - 1 x Audio jack (Line-in, Line-out, Mic)
 - 1 x DisplayPort connectors
 - 1 x HDMI
 - 1 x VGA
 - 1 x PS2 KB/MS
 - 2 x USB 2.0
 - 1 x RJ-45
 - 4 x USB 3.2 Gen 1 (5Gb/s)
- ◆ Front Audio: 2 x 5-pin pin header
- ◆ TPM: 1 x TPM (2x10 pin)
- ◆ 80 port: 2 x 7 segment display
- ◆ Front Panel
 - 1 x Front panel (2x7 pin, power LED, HDD LED, speaker/buzzer, power button, reset button)
- ◆ I²C: 1 x 4-pin wafer
- ◆ SMBus: 1 x 4-pin wafer
- ◆ Internal storage
 - EEPROM (supports EAPI R1.0)
- ◆ Watchdog Timer
 - Software programmable supports 1~255 sec system reset
- ◆ GPIO: 8-bit GPIO
- ◆ Power Supply
 - ATX / AT Power Supply
 - 24+4 pins
- ◆ Fan Connector
 - 1 x 4-pin / 1 x 3-pin CPU module fan connector
 - 1 x 3-pin system fan connector by SIO
- ◆ Operating Temperature: -20°C ~ 60°C
- ◆ Storage Temperature: -30°C ~ 70°C
- ◆ Operating Humidity
 - 5% ~ 95 non-condensing
- ◆ Dimensions
 - 304.8 mm x 243.8 mm (12" x 9.6")
- ◆ Weight: GW:650g / NW:430g
- ◆ CE/FCC compliant

Dimensions (Unit: mm)



Packing List


1 x COM Express baseboard	1 x Mini jumper pack
2 x SATA cable	1 x QIG

Ordering Information

Part No.	Description
ICE-DB-T6R-R11	Baseboard for COM Express Type 6 Module COM.0 Rev. 2.1, support PICMG EAPI R1.0
32102-000100-200-RS	SATA power cable, MOLEX 5264-4P to SATA15P

TYPE 6

ICE-DB-T6

Baseboard for COM Express Type 6 Module
(for ICE-QM770 & ICE-CV-D25501/N26001)


Features

- ATX form factor baseboard for COM Express Rev. 2, Pin-out Type 6
- Supports one PCIe x16, six PCIe x1 and two PCIe Mini
- Supports smart battery charger

Specifications

- ◆ Form Factor: ATX form factor baseboard
- ◆ CPU
 - Supports COM Express Compact/Mini module using connector pin out Type 6
- ◆ Display Interfaces
 - 1 x 18/24-bit single/dual-channel LVDS
 - 1 x VGA
 - 3 x DisplayPort (2 x real connectors, 1 x pin header)
- ◆ Super I/O: W83627DHG
- ◆ Audio
 - Realtek ALC892 HD Audio codec (Line-in, Line-out, Mic)
- ◆ Expansion
 - 1 x LPC
 - 2 x PCIe Mini (with USB)
 - 1 x PCIe x16
 - 6 x PCIe x1
- ◆ Internal I/O Interface
 - 1 x PS2 KB/MS
 - 2 x RS-232 from SIO
 - 1 x SD
 - 2 x USB 2.0
 - 4 x SATA port
 - 2 x RS-232 from COM Express (only TX, RX and GND)
- ◆ External I/O Interface
 - 1 x VGA
 - 4 x USB 3.2 Gen 1 (5Gb/s)
 - 1 x RJ-45
 - 3 x DisplayPort
 - 1 x Audio jack (Line-in, Line-out, Mic)
- ◆ Front Audio: 1 x Front audio (2x5 pin)
- ◆ TPM: 1 x TPM (2x10 pin)
- ◆ 80 port: 2 x 7 segment display
- ◆ Front Panel
 - 1 x Front panel (2x7 pin, power LED, HDD LED, speaker/buzzer, power button, reset button)
- ◆ I²C: 1 x 4-pin wafer
- ◆ SMBus: 1 x 4-pin wafer
- ◆ Watchdog Timer
 - Software programmable supports 1~255 sec. system reset
- ◆ GPIO: 8-bit GPIO (GPIO from iWDD co-lay SIO)
- ◆ Power Supply: ATX/AT power supply
- ◆ Battery: Supports smart battery charger connector
- ◆ Fan Connector
 - 1 x 4-pin / 1 x 3-pin CPU module fan connector
 - 1 x 3-pin system fan connector by SIO
- ◆ Operating Temperature: -10°C ~ 60°C
- ◆ Storage Temperature: -20°C ~ 70°C
- ◆ Operating Humidity
 - 5% ~ 95%, non-condensing
- ◆ Dimensions
 - 304.8 mm x 243.8 mm (12" x 9.6")
- ◆ Weight: GW:660g / NW:450g
- ◆ CE/FCC compliant

Dimensions (Unit: mm)



Packing List

1 x COM Express baseboard	1 x Mini jumper pack
1 x Dual-port RS-232 cable	1 x QIG
2 x SATA cable	1 x QIG

Ordering Information

Part No.	Description
ICE-DB-T6-R10	Baseboard for COM Express Type 6 modules
19800-000082-RS	RS-232/422/485 cable, 14-pin to dual DB-9, 230mm, P=2.54
32102-000100-200-RS	SATA power cable, MOLEX 5264-4P to SATA15P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IEI:

[ICE-DB-T6-R10](#) [ICE-DB-T6R-R11](#)