




used for: D-SUB

No. of pos.	A ^{+0.2}	B ^{+0.2}	C	D1 ^{+0.25}	E ^{-0.30}	Part-No.
9	21.1	39.4	25.00 ^{+0.12} _{-0.13}	16.79	5.62	4STD09PAR99E20X
15	21.1	47.7	33.30 ^{+0.15} _{-0.1}	25.12	5.62	4STD15PAR99E20X
25	21.1	61.4	47.04 ^{+0.13}	38.84	5.49	4STD25PAR99E20X
37	21.1	77.9	63.50 ^{+0.13}	55.30	5.49	4STD37PAR99E20X



NOTES:

- METALSHELLS: COPPER ALLOY; min. 320µ" TIN
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8µ" HARD GOLD OVER min. 50µ" NICKEL
- THREADED SPACER CLIP: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
PCB-HOLE: Ø3.1±0.1; PCB THICKNESS 1.6mm
- COLLAR: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
- P.C.B. HOLE DRILLINGS ON DRAWING NO.: 16K11IUA
- MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC
- = CHECK DIMENSION

Directive 2002/95/EC
RoHS
Compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance				scale: 2:1			
								material: SEE NOTES			
				1999	date	name		title: D-SUB MALE SOLDER PIN STRAIGHT 9-37pos. WITH THREADED SPACER CLIP WATERTIGHT			
				drawn	12.05.	Barcinski					
				appd.	12.05.	Mickenbecker					
				norm	DIN 41652						
				d-old							
						dwg no: CAD/ REL.14		DIN-A			
								18K21B9A		3	
										sh: 1/1	
rev.	description		date	name		product no:		SEE TABLE			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

4STD25PAR99E20X