

**产品名称: 6V 6公斤模拟舵机 Product Name: 6V 6kg.cm Analog Servo****产品型号 Model No.FS5106B****1.使用环境条件 Apply Environmental Condition**

No.	Item	Specification
1-1	存储温度 Storage Temperature Range	-30℃~80℃
1-2	运行温度 Operating Temperature Range	-15℃~70℃

2.测试环境 Standard Test Environment

No.	Item	Specification
2-1	温度 Temperature range	25℃ ±5℃
2-2	湿度 Humidity range	65%±10%

3.机械特性 Mechanical Specification

No.	Item	Specification
3-1	尺寸 Size	A: 40.8mm B: 20.1mm C: 38mm D: 49.5mm
3-2	重量 Weight	40g ±0.2 (1.41oz)
3-3	齿轮类型 Gear type	Plastic Gear(Nylon & POM)
3-6	机构极限角度 Limit angle	200° ±5°
3-7	轴承 Bearing	2 Ball bearings
3-8	出力轴 Horn gear spline	25T
3-9	摆臂 Horn type	Plastic,POM
3-10	外壳 Case	Nylon & Fiberglass
3-11	舵机线 Connector wire	300mm ±5 mm
3-12	马达 Motor	Metal brush motor
3-13	防水性能 Splash water resistance	NO

4.电气特性 Electrical Specification (Function of the Performance)

No.	工作电压 Operating Voltage Range	4.8V	6V
4-1*	静态电流 Idle current(at stopped)	5mA	7mA
4-2*	空载速度 No load speed	0.18sec/60°	0.16 sec/60°
4-3*	空载电流 Runnig current(at no load)	160 mA	190 mA
4-4	堵转扭矩 Peak stall torque	5kg.cm	6kg.cm
		69.56oz.in	83.47oz.in
4-5	堵转电流 Stall current	980 mA	1100mA

Note: "*"definition is average value when the servo runing with no load



FEETECH RC Model Co.,Ltd.

产品规格书

Specification of Product

V1.0 Page 1/2


产品名称: 6V 6公斤模拟舵机 Product Name: 6V 6kg.cm Analog Servo

产品型号 Model No.FS5106B

5.控制特性 Control Specification:

No.	Item	Specification
5-1	控制信号 Command signal	Pulse width modification
5-2	放大器类型 Amplifier type	Analog comparator
5-3	脉冲宽度范围 Pulse width range	700~2300 μ sec
5-4	中立位置 Neutral position	1500 μ sec
5-5	旋转角度 Running degree	180° ($\pm 5^\circ$) (when 700~2300 μ sec)
5-6	死区宽度 Dead band width	5 μ sec
5-7	旋转方向 Rotating direction	Counterclockwise (when 1000~2000 μ sec)

6.外形图 The Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[ROB-11965](#)