

Wireless Hi Power Transmitter Module (RF ASK)



Version History

Version	Date	Changes
V1.01	Mar. 01, 2002	1 st . Edition
V1.02	Jul. 05, 2008	2 nd . Edition
V1.03	Oct. 20, 2010	3 rd . Edition

Model : TWS-BS-6

- Frequency Range: 315MHz
- Modulate Mode: ASK
- Circuit Shape: SAW
- Data Rate: 8Kbps
- Supply Voltage: 1.5~12V
- Output Power : 14dBm
- Working temperature: -20~+85℃
- Solder temperature: 230℃(10 seconds).
- High sensitivity is designed.

Application

● Wireless Data Transmission	● Wireless Game Pad
● Remote Control	● Wireless Toys
● Car Key	● Home Automation
● AMR- Automatic Meter Reading	● Remote Keyless Entry

Absolute Maximum Rating

Rating	Value	Unit
Power Supply and All Input/ Output Pins	-0.3~+12.0	V
Non-Operating Case Temperature	-20~+85	℃
Soldering Temperature(10 seconds)	230	℃

Electrical Characteristic


Characteristic	Min	Type	Max	Unit
Operating Frequency ($\pm 250\text{KHz}$)	314.75	315.00	315.25	MHz
Data Rate			8	Kbps
Current Consumption			8	mA
Output Power			32	mW
Operating Voltage	3		12	VDC
Operating Ambient Temperature	-20		+85	°C

Pin Assignment


Pin	Function
1	GND
2	Data in
3	Vcc
4	ANT



Size



Demo Circuit



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[WRL-10535](#)