

1. DESCRIPTION & PHOTO OF PRODUCT



View

2. CHARACTERISTICS

2.1 ELECTRICAL CHARACTERISTICS

Rated Voltage	5VDC
Operating Voltage	4.5~5.5VDC
Starting Voltage	4.5V
Rated Current	0.13±10%A
Power Input	0.65W
Fan Speed	2800±500RPM
Air Flow	2.01CFM
Noise	21dB-A
Bearing Type	ERB

2.2 MECHANICAL CHARACTERISTICS

Fan Dimension	Φ 36X9
Heatsink Dimension	55X37.2X11.5
Overall Dimension	55X37.2X12
Heatsink Material	Aluminum
Weight	23.3 g

3. FAN SPECIFICATIONS

Model No.: R054010SLZI326aR(EBR)

Fan Dimension: Φ 36X9

Rated Voltage: 5 VDC

Operating Voltage: 4.5~5.5 VDC

Started Voltage: DC 4.5V

Rated Current: 0.13 $\pm$ 10%A

Rated Power: 0.65W

Bearing Type: EAB

Fan Speed: 2800 $\pm$ 500 RPM

Air Flow: 2.01CFM

Static pressure: 0.54mmH₂O

Acoustical Noise: 21 dB(A)

Background Noise 17.8dB(A)


Operating Temperature: -10°C ~ +60°C (65%RH)

Storage Temperature: -20°C ~ +70°C (65%RH)

Weight: 7.5 g

PG

7

[illegible]

Tolerance as below, unless otherwise specified			
DIMENSION	0.5~3	>3~6	>6~30
TOLERANCE	+0.2	+0.3	+0.5
			+0.8
			+1.2
			+2
			+400~1000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AAEON:

EP-FNUPACTCLRDC