



UP²

bridge the gap

specification



UP² (UP Squared) is world's fastest maker board with the high performance and low power consumption features of **Intel® Celeron™ and Pentium™ Processors (codename Apollo Lake)**.

The internal GPU is the new **Intel Gen 9 HD with 12 / 18 Execution Units**, supporting **4K Codec Decode and Encode** for HEVC⁴, H.264 and VP8. Thanks to the Vector Units Image Processing Unit and Precision Timing Management to synchronize CPU with I/O, improved determinism (cache QoS, Intel Virtualization Technology), all the graphic processing is effortless to UP² (UP Squared).

UP² (UP Squared) comes with **2GB/4GB/8GB LPDDR4** and **32GB/64GB/128GB eMMC**. A **40-pin GP-bus** provides the freedom for makers to build up their module. Additionally, there is a **60-pin EXHAT** for embedded applications. This allows for the exploration of more possibilities. The expansion capabilities of UP² (UP Squared) goes much further than this. Native **mini-PCI-e, M.2 2230 and SATA3** are all built in on the board. What more could one desire?

The board supports **Windows 10, Windows IoT Core, Ubilinux, Ubuntu, Yocto and Android Marshmallow**. It's really UP to you to decide which operating system is best for your application. Now, all you need is an UP² (UP Squared) to begin your project!

UP - Applications




Drones




Education



Robotics



Media Center




Internet of Things



Home Automation

 	<p>SOC Intel® Celeron™ N3350 (up to 2.4 GHz) Intel® Pentium™ N4200 (up to 2.5 GHz)</p> <p>Graphics Intel® Gen 9 HD, supporting 4K Codec Decode and Encode for HEVC4, H.264, VP8</p> <p>Video & Audio HDMI 1.4b x2 4K @ 30 hz I2S audio port</p> <p>Camera interface CSI 2-lane CSI 4-lane</p> <p>Display interface eDP</p> <p>Power 5V DC-in @ 4A 5.5/2.1mm jack</p> <p>Operating humidity 10%~80%RH non-condensing</p> <p>Operating Temperature 32-140°F / 0~60°C</p>	 	<p>Memory 2GB / 4GB / 8 GB LPDDR4</p> <p>Storage Capacity 32 GB / 64 GB / 128 GB eMMC</p> <p>USB 3x UB3.0 (Type A) + 1x USB 3.0 OTG (Micro B) 2x USB2.0+2 X UART (Tx/Rx) debug port (pin header)</p> <p>Ethernet 2x Gb Ethernet (full speed) RJ-45</p> <p>RTC Yes</p> <p>Expansion 40 pin General Purpose bus 60 pin EXHAT 1xmini-PCIe , M.2 2230, SATA3</p> <p>Compatible Operating system Microsoft Windows 10 (full), Windows IOT Core, Linux (ublinux, Ubuntu, Yocto), Android Marshmallow</p> <p>Dimensions 3.37" x 3.54" / 85.60 mm x 90 mm</p> <p>Certificate CE/FCC Class A, RoHS complaint, REACH</p>
------------------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	------------------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------



UP - Pinout

2	4	6	8	10	12	14	16	18	20	22	24	26	28	30	32	34	36	38	40
1	3	5	7	9	11	13	15	17	19	21	23	25	27	29	31	33	35	37	39
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40

Part number : UPS-APLC2-A10-0216 UPS-APLC2-A10-0232 UPS-APLC2-A10-0432	Intel® Celeron™ N3350 - 2 GB + 16 GB eMMC Intel® Celeron™ N3350 - 2 GB + 32 GB eMMC Intel® Celeron™ N3350 - 4 GB + 32 GB eMMC	UPS-APLP4-A10-0432 UPS-APLP4-A10-0864 UPS-APLP4-A10-08128	Intel® Pentium™ N4200 - 4 GB + 32 GB eMMC Intel® Pentium™ N4200 - 8 GB + 64 GB eMMC Intel® Pentium™ N4200 - 8 GB + 128 GB eMMC
---------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------	--------------------------------------------------------------------------------------------------------------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AAEON:](#)

[RE-UPS-APLC2-0232-PACK02](#) [RE-UPS-APLC2-0432-PACK02](#) [RE-UPS-APLP4-0432-PACK02](#) [RE-UPS-APLP4-0864-PACK02](#) [RE-UPS-APLX7-0464-PACK02](#) [RE-UPS-X70464-RBM01](#)