

## SUCOFLEX® 526S Microwave Cable Assembly

### Description

SUCOFLEX 526S microwave cable assemblies set a new measurement standard through 26.5 GHz.

- Excellent return and insertion loss
- Phase and amplitude stability with flexure and movement
- Torque, crush and kink resistance
- Precise and repeatable measurements
- Long service life
- Reduce total cost of test with durable, reliable performance



### Product Configuration

Description	SF526S/11N/11N/1000mm
Item number	85089172
Cable type	SUCOFLEX 526S
Length of assembly	1'000 mm
Connector A	11_N (straight male)
Connector B	11_N (straight male)

### Technical Data

#### Mechanical Data

Outer diameter	7.7 mm
Min. bending radius	25.4 mm
Weight	235 g
Crush resistance	26 kgf /cm


#### Environmental Data

Operating temperature	-55 ... + 75°C
RoHS, REACH	Compliant


#### Electrical Data

Impedance	50 $\Omega$
Operating frequency	up to 18.0 GHz
Velocity of propagation	77 %
Time delay	4.3 ns / m
Typical return loss	-25.0 dB
Min. return loss	-19.0 dB
Typical insertion loss	1.32 dB
Max. insertion loss	1.43 dB
Screening effectiveness	> 90 dB
Typ. amplitude stability vs. shaking	$\pm 0.05$ dB
Typ. amplitude stability vs. bending	$\pm 0.05$ dB
Typ. phase stability vs. bending	$\pm 3.0^\circ$

SUCOFLEX® 526S  
Microwave Cable Assembly



Connector 11\_N (straight male)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[SF526S/11N/11N/1000mm](#)