

Coaxial Cable Connector

11_XQN-50-4-1/133_NE

Description

Straight cable plug

Interface standards

QN QLF compliant

Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	32.5 dB	25.5 dB	24.4 dB

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.024492 kg

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	EPDM (Ethylene propylene diene rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00285356
-----------------	--------------

Ordering Information

Single package	11_XQN-50-4-1/133_NE
----------------	----------------------

Additional Information

Suitable cables	SPUMA_240, SPUMA_240-FR-01, Spuma_240-RS-FR
-----------------	---

Remarks

Sold as Cable Assembly only

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

11_XQN-50-4-1/133_NE