

## Coaxial Cable Connector 24\_BNC-50-3-5/133\_N

### Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0179 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00008943
Catalogue drawing	DCA-00008945
Assembly instruction	DOC-0000179064
Mounting hole	DOU-00008751

### Ordering Information

Single package	24_BNC-50-3-5/133_NE
----------------	----------------------

### Additional Information

Suitable cables	RG_58_C/U, RG_223_/U, ENVIROFLEX_142, RG_400_/U
-----------------	---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[24\\_BNC-50-3-5/133\\_NE](#)