

Between Series Adaptor 32_MMCX-SMA-50-1/111_O

Description

Adaptor plug/plug
MMCX plug (male) / SMA plug (male)

Interface standards
Series MMCX - SUHNER-MMCX
Series SMA - IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	6 GHz	
Frequency range	DC to 2.5 GHz	2.5 to 6 GHz
Return loss	≥ 26 dB	≥ 21 dB

Mechanical Data

Number of matings	500
Weight	0.0058 kg

Environmental Data

Operating temperature	-55 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - MMCX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Interface - SMA plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Coupling nut	Bronze	Gold Plating (without Nickel underplating)
Gasket	VMQ (Silicone rubber)	

Related Documents

Catalogue drawing	DCA-00014512
-------------------	--------------

Ordering Information

Single package	32_MMCX-SMA-50-1/111_OE
----------------	-------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[32_MMCX-SMA-50-1/111_OE](#)