

LOCTITE ECCOBOND FP4470

March 2017

PRODUCT DESCRIPTION

LOCTITE ECCOBOND FP4470 provides the following product characteristics:

Technology	Epoxy
Appearance	Black
Filler Weight, %	75
Product Benefits	<ul style="list-style-type: none"> • High purity • 260°C reflow capability for Pb-free applications • Green product • Excellent flow properties
Cure	Heat cure
Application	Encapsulant
Typical Package Application	BGA, Chip scale packages, PBGA and Full arrays on LTCC
Operating Temperature	-65 to 150 °C

LOCTITE ECCOBOND FP4470 features excellent flow properties allowing the material to penetrate fine pitch wires and deep cavities without entrapping voids. This product can withstand solder reflow after being exposed to JEDEC Level 2A (60°C/60% RH, 120 hours) preconditioning.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Brookfield - RVF, 25 °C, mPa·s (cP):	
Spindle 6, speed 10 rpm	42,000
Specific Gravity @ 25 °C	1.8
Pot Life @ 25°C, days	3
Shelf Life @ -40°C, days	274
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE

Gel Time

12 minutes @ 121°C

Cure Schedule

30 minutes @ 125°C + 90 minutes @ 165°C

LOCTITE ECCOBOND FP4470 should be dispensed onto a substrate warmed to approximately 75°C.

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Coefficient of Thermal Expansion, ppm/°C:	
Below T _g (40 to 80°C)	18
Above T _g (170 to 210°C)	65
Glass Transition Temperature (T _g) by TMA, °C	148

Extractable Ionic Content @ 121 °C, ppm:

Chloride (Cl ⁻)	<2
Sodium (Na ⁺)	<2
Potassium (K ⁺)	1

Flexural Modulus :

@ 25°C	N/mm ²	12,700
	(psi)	(1.84×10 ⁶)
@ 240°C	N/mm ²	600
	(psi)	(87,000)

Flexural strength, ASTM D790:

@ 25°C	N/mm ²	137,000
	(psi)	(1.99×10 ⁷)
@ 240°C	N/mm ²	17,000
	(psi)	(2.47×10 ⁶)

Electrical Properties

Volume Resistivity, IEC 60093, Ω·cm	5×10 ¹⁶
Dielectric Constant / Dissipation Factor@ 1 MHz	3.5/0.01

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

THAWING:

1. Allow container to reach room temperature before use.
2. After removing from the freezer, set the syringes to stand vertically while thawing.
3. Warm at room temperature until no longer cool to the touch (normally 60 to 90 minutes).
4. DO NOT thaw in an oven.

DIRECTIONS FOR USE

1. For best results, dispense onto substrate warmed to 75°C.
2. Once dispensed, material should be cured within 30 minutes to prevent moisture contamination.
3. The cured properties of moisture contaminated material will be poorer than those described.
4. **NOTE:** Elevated temperatures reduce working life.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: -40°C. Storage below -40°C or greater than -40°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If

additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$

$\text{kV/mm} \times 25.4 = \text{V/mil}$

$\text{mm} / 25.4 = \text{inches}$

$\text{N} \times 0.225 = \text{lb}$

$\text{N/mm} \times 5.71 = \text{lb/in}$

$\text{psi} \times 145 = \text{N/mm}^2$

$\text{MPa} = \text{N/mm}^2$

$\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$

$\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$

$\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$

$\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 2

Americas
+1.888.943.6535

Europe
+32.1457.5611

Asia
+86.21.3898.4800

For the most direct access to local sales and technical support visit: www.henkel.com/electronics

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[468135](#) [556652](#) [601159](#) [555621](#)