

LOCTITE ECCOBOND FP4545FC

August 2019

PRODUCT DESCRIPTION

LOCTITE ECCOBOND FP4545FC provides the following product characteristics:

Technology	Epoxy
Appearance	Black
Product Benefits	<ul style="list-style-type: none"> • High purity • Forms a rigid, low stress seal • Low CTE • Good toughness • Improved toughness
Filler Weight, %	55
Components	One-component
Cure	Heat cure
Application	Underfill
Typical Applications	Flip Chip

LOCTITE ECCOBOND FP4545FC epoxy encapsulant designed as underfill and helps dissipate stress on solder joints and extends thermal cycling performance. This material is specially suited for flip-chip devices requiring improved crack/fracture resistance and no-clean flux compatibility.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Brookfield - Cone & Plate, 25 °C, mPa·s (cP):	
cp #52, Speed 20, rpm	6,500
Rheology @ 90 °C,	1.5
Pot life @ 25°C, hours:	
(Time required to double viscosity)	12
Gel Time @ 121 °C, minutes	16
Shelf Life @ -40°C, days	274
Flow Rate @ 100°C, seconds	30
500mil travel, 3mil gap	
Specific Gravity	1.6
Work Life, hours	8
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE

Recommended Cure Schedule

60 minutes @ 165°C

Alternate Cure Schedule

120 minutes @ 170°C
(Enhanced Performance)

The above cure profile is a guideline recommendation. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Coefficient of Thermal Expansion, ppm/°C:	
Below Tg	28
Above Tg	100
(Cured 120 minutes @ 165°C)	
Glass Transition Temperature(Tg), °C	120
Flexural Modulus, ASTM D790	N/mm ² 7,100
	(psi) (1,029,500)
Extractable Ionic Content, :	
Chloride (Cl-)	20
Sodium (Na+)	5

TYPICAL ENVIRONMENTAL RESISTANCE

Outgassing Properties

Outgassing, NASA Outgassing:	
TML, %	0.23
CVCM, %	<0.01
WVR, %	0.17

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

THAWING:

1. Store tip down and warm at room temperature until no longer cool to the touch (normally 60 to 90 minutes).
2. Frozen packages must be completely thawed before use.
3. DO NOT thaw in an oven.

Directions for use

1. To encapsulate flip chips by capillary action, the chip and substrate must be thoroughly cleaned.
2. For best results, the material should be dispensed onto a substrate that has been preheated to approximately 100 to 120°C and held at that temperature until flow stops.
3. Devices with wet encapsulant should not be exposed to humidity in the air.
4. If the material cannot be initially gelled to a hard finish within 1 hour after dispensing, storage in desiccator cabinet is suggested until full curing is possible.
5. A bead of LOCTITE ECCOBOND FP4545FC is then applied to one or two sides (L-shape) of the chip perimeter.

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage : -40 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$

$\text{kV/mm} \times 25.4 = \text{V/mil}$

$\text{mm} / 25.4 = \text{inches}$

$\text{N} \times 0.225 = \text{lb/F}$

$\text{N/mm} \times 5.71 = \text{lb/in}$

$\text{psi} \times 145 = \text{N/mm}^2$

$\text{MPa} = \text{N/mm}^2$

$\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$

$\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$

$\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$

$\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[945398](#)