

## RF TERMINATION Type 6515.19.A

### Description

Standard Termination, Medium Power



### Product Configuration

Connector	SMA plug (male)
Interface standards	IEC 60169-15_MIL-STD-348A/310_CECC 22110

### Technical Data

#### Electrical Data

Nominal Impedance	50 $\Omega$			
Frequency range	0 to 12.4 GHz			
Frequency sub range	DC to 1 GHz	1 to 4 GHz	4 to 10 GHz	10 to 12.4 GHz
VSWR max.	1.05	1.1	1.2	1.25
Power rating	15 Watt average power up to 25 °C ambient temperature, linearly derated to 0 Watt at 130 °C ambient temperature. 1000 Watt peak power , 5 $\mu$ s pulse, 0.05 % duty cycle			

#### Mechanical Data

Weight	0.081 kg
--------	----------

#### Environmental Data

Operating temperature	-40 °C to 130 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Part	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Aluminium	
Insulator	PFA / PTFE	
Coupling nut	Bronze	Gold Plating (Nickel underplated)

### Related Documents

Outline drawing	DOU-00020129
-----------------	--------------

### Ordering Information

Single Packaging	6515.19.A
Packaging	

### Additional Information

Important note	WARNING Beryllia Ceramic Inside! DO NOT sand, scrap or tamper with. Dispose in accordance with all relevant regulations.
----------------	--

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[6515.19.A](#)