

LOCTITE EDAG 1415M E&C

June 2021

PRODUCT DESCRIPTION

LOCTITE EDAG 1415M E&C provides the following product characteristics:

Technology	Thermoplastic
Appearance	Silver
Operating Temperature	105 °C
Product Benefits	<ul style="list-style-type: none"> • Maintains low resistance after exposure to the elements • Does not require primer or top coat • Easily applied by spray or brush
Cure	Air dry
Application	Conductive coating

LOCTITE EDAG 1415M E&C shielding coating is designed to provide electromagnetic compatibility (EMC). It is compatible with plastics commonly used for electronic equipment enclosures.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Solids Content, %	58
Viscosity, Brookfield, 20 °C, mPa·s (cP):	
Speed 20 rpm	375
Density, Kg/m ³	1,630
Theoretical coverage @ 10µm coating thickness, 9 m ² /kg	
Shelf Life @ 5 to 30°C, months (from date of qualification in original seal)	18
Flash Point, °C	14

TYPICAL DRYING CYCLE

Recommended Drying Cycle

30 minutes @ 70 to 80°C

For production runs, conventional forced drying methods may be used for faster processing. Forced drying of the coating will noticeably improve conductivity.

LOCTITE EDAG 1415M E&C dries to touch in about 10 minutes and can be handled after a further approximately 10 minute hold, depending on ambient temperature.

Good coating properties will be achieved after 4 to 8 hours air drying, depending on coating thickness and temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Sample tested @ 25µm coating thickness

Electrical Properties

Attenuation @ 1,000 MHz, dB	60
Sheet Resistance, ohms/sq	<0.015

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

DIRECTIONS FOR USE

1. Surface Preparation

- Surface to be coated must be dry and free on contaminants such as oil or chemical residues.

2. Mixing/Dilution

- Thoroughly homogenize LOCTITE EDAG 1415M E&C before use. Check to make sure there are no unmixed solids at the bottom of the container
- Recommended dilution ratio(s) as follows:
Brush Application: Use LOCTITE EDAG 1415M E&C neat
Spray Application:
 - Use MEK/Diacetone alcohol blend
 - By Weight: 2 part(s) product to 1 part(s) solvent
- If the evaporation speed of this mixture is too high, reduce the amount of Methyl ethyl ketone (MEK)

3. Application

- When applying LOCTITE EDAG 1415M E&C by spray, a conventional paddle-agitated pressure tank system should be used.
- It is recommended to maintain a spray pressure of 2 to 2.5 bar with a nozzle diameter varying from 1 to 1.5 mm.
- Small prototype runs may be sprayed with well-mixed product, using suction cup spray equipment.
- A 10 to 15µm coating thickness is recommended for good EMI shielding performance.
- Avoid dry spraying for maximum adhesion and conductivity.

Storage

Store product in the unopened container in a cool dry well ventilated area. Storage information may be indicated on the product container labeling.

Optimal Storage : 5 to 30 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel Representative.

Empty containers may retain hazardous properties.

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Conversions

(°C x 1.8) + 32 = °F
kV/mm x 25.4 = V/mil
mm / 25.4 = inches
N x 0.225 = lb/F
N/mm x 5.71 = lb/in
psi x 145 = N/mm²
MPa = N/mm²
N·m x 8.851 = lb·in
N·m x 0.738 = lb·ft
N·mm x 0.142 = oz·in
mPa·s = cP

Disclaimer

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned

by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1395599](#)