

LOCTITE EDAG 550 E&C

June 2017

PRODUCT DESCRIPTION

LOCTITE EDAG 550 E&C provides the following product characteristics:

Technology	Acrylic
Appearance	Gray
Filler Type	Nickel
Diluent	LOCTITE SB-1 E&C or LOCTITE SB-10 E&C, depending on substrate
Cure	Heat cure
Operating Temperature-Maximum	149°C
Product Benefits	<ul style="list-style-type: none"> Conductive
Application	Conductive Ink
Typical Assembly Applications	EMI shielding of plastic cabinetry used in electronic equipment

LOCTITE EDAG 550 E&C conductive coating is formulated to provide long term shielding and grounding properties against electro-magnetic interference (EMI). When diluted with the proper solvent, LOCTITE EDAG 550 E&C can be easily applied by spray onto plastics commonly used in electronic equipment cabinet assembly. This product can also be overcoated by decorative top coatings with minimum affect on the shielding and decorative coating properties.

TYPICAL PROPERTIES OF UNCURED MATERIAL AS SPRAYED

Solids Content by Weight, %	59.5
Density, kg/l	1.62
Viscosity, Brookfield, mPa·s (cP):	
Spindle 4, speed 20 rpm	7,500
Theoretical coverage @ 25µm, m ² /kg	6.39
Shelf Life @ 32°C (from date of manufacture), days	730
Flash Point - See SDS	

TYPICAL DRYING CYCLE

Recommended Dry Film Thickness

Dry Film Thickness, µm	51 to 63.6
------------------------	------------

Recommended Drying Cycle

16 hours air dry @ 60 to 71°C

Percent Volatiles

VOC, g/l	656
----------	-----

The above profiles are guideline recommendation. Conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer drying equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Attenuation @ 2 mils, dB	60 to 65
--------------------------	----------

Electrical Properties

Resistivity, ohms/sq/mil	0.9
--------------------------	-----

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

DIRECTIONS FOR USE

Surface Preparation

- Surfaces to be coated must be clean, dry and free of dust.

Mixing/Dilution

- Thoroughly mix in a paint shaker before use.
- LOCTITE EDAG 550 E&C is a slow/soft settling material. Mixing time can be substantially reduced when compared to conventional nickel coating.
- For proper dilution, use a ratio of 1 : 0.8, product : solvent by volume.

Application

- LOCTITE EDAG 550 E&C should be applied by spray using conventional propeller agitated pressure pot spray systems.
- Small prototype runs may be sprayed with well-mixed product, using suction cup spray equipment.
- A nominal 51 to 63.6 µm dry coating thickness is recommended for good shielding performance. However, a thinner coating may be acceptable, depending on the shielding requirements of the device being protected.
- Avoid dry spraying for maximum adhesion and conductivity.
- During humid days, the addition of no more than 6 fluid ounces per gallon of diacetone alcohol or butyl alcohol to LOCTITE EDAG 550 E&C will eliminate blushing. The blushing is characterized by a white tint to the dried surface.

Drying

- LOCTITE EDAG 550 E&C dries to touch in about 5 minutes; to handle in approximately 30 minutes, depending on ambient temperature and coating thickness.
- The product may be force dried beginning with a 20-minute flash-off, then 30 minutes at 60° to 71°C.

Mask Cleaning

- For high volume production where masks are used to prevent coating certain areas, the masks can be cleaned with lacquer thinner or ketone solvents.

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Store in a cool, well ventilated area.

Optimal Storage : 32 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before

repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Reference 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1959116](#)