

SENCITY® Antenna down- and sidetilt Bracket 9091.99.0274

Description

Down- and sidetilt bracket accessory for SENCITY planar antennas
For outdoor and indoor applications

Two hose clamps for pole mount option included



Technical Data

Mechanical Data

Weight	0.1 kg
Dimensions (mm)	55 x 42 x 40 (Height x Width x Depth)
Mast diameter (mm)	30 - 155
Material	Stainless Steel

Max. tractive force 20 N in x/y/z direction


Mounting material 2 screws M4 L=8mm and 2 Quick Release hose clamps for pole-diameter 30 to 155 mm

Environmental Data

Operation temperature (°C)	-40 to 85
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Related Documents

Mounting instruction	DOC-0000834560
Painting instruction	DOC-0000256180
Security instruction	DOC-0000278984
Outline drawing1	DOU-00375681



Quick hose clamps		Clamping Range			
Description	Item number	Min. Dia (in.)	Max. Dia (in.)	Min. Dia (mm.)	Max. Dia (mm.)
HOSE_CLAMP_30x155_01_02 (Set)	84076411	1 3/16	6 1/8	30	155

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

9091.99.0274