

LOCTITE EDAG 6041 E&C

October 2014

PRODUCT DESCRIPTION

LOCTITE EDAG 6041 E&C provides the following product characteristics:

Technology	Thermoset Resin
Appearance	Silver
Filler Type	Silver
Cure	Hot air drying and Heat cure
Product Benefits	<ul style="list-style-type: none">• Conductive
Application	Conductive coating
Key Substrates	Phenolic paper, Epoxy paper and Glass epoxy
Typical Assembly Applications	terminations on potentiometer tracks

LOCTITE EDAG 6041 E&C is designed to dry rapidly to form a flexible, conductive coating.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Solids Content, %	67
Viscosity, Brookfield, 20 °C, mPa·s (cP):	
Speed 20 rpm	1,200
Density, Kg/m ³	1,990
Theoretical coverage @ 10µm coating thickness, m ² /kg	14
Shelf Life (from date of qualification in original seal), days	365
Flash Point, °C	28

TYPICAL DRYING and CURE CYCLE

Allow to dry in air until the coating is dry to touch, then oven cure 30 to 60minutes @ 150°C.

The best properties are obtained after 60 minutes.

The above drying profile is a guideline recommendation. Conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer drying equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Electrical Properties:

Sheet Resistance @ 25µm dry coating thickness,	<0.01
ohms/sq	

GENERAL INFORMATION

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

DIRECTIONS FOR USE

1. Surface Preparation

- Surfaces to be coated must be clean, dry and free of dust

2. Application

- LOCTITE EDAG 6041 E&C may be applied by Brush, spray or other methods method.

3. Spray Application

- If applied by spray, LOCTITE EDAG 6041 E&C should be diluted with 1 part by weight of diluent to 3 parts of product.
- Stir thoroughly before dilution and use and make sure no deposit is left on the bottom of the container.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Store in a cool, well ventilated area.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Conversions

(°C x 1.8) + 32 = °F
kV/mm x 25.4 = V/mil
mm / 25.4 = inches
N x 0.225 = lb
N/mm x 5.71 = lb/in
N/mm² x 145 = psi
MPa = N/mm²
MPa x 145 = psi
N·m x 8.851 = lb·in
N·m x 0.738 = lb·ft
N·mm x 0.142 = oz·in
mPa·s = cP

Disclaimer

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials

to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada, Inc. the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1239077](#)