


ATEX RF SPD 9096.26.0601

Description

ATEX RF SPD GDT technology

Benefits

Type of protection: "nA" and "tc"
For Zone 2 or Zone 22 of potentially explosive atmospheres
The protector can also be installed reversely
DC continuity for remote powering
Fix installed GDT, static sparkover-voltage nom. 200 V
Compliant to IEC 61643-21



Product Configuration

Main path connectors Port 1: unprotected, TNC plug (male) - Port 2: protected, TNC jack (female)
Mounting and grounding MH4 (bulkhead mounting), brk (bracket)

Technical Data

Electrical Data

Impedance	50 Ω		
Frequency range	0 - 5800 MHz	0 - 5600 MHz	5600 - 5800 MHz
Return loss	≥ 18.5 dB	≥ 20 dB	≥ 18.5 dB
Insertion loss	≤ 0.2 dB	≤ 0.2 dB	≤ 0.2 dB
RF CW power	≤ 6 W		
PIM 3rd order	not specified		
DC supply voltage	≤ 48 V		
DC current	≤ 1 A		
Surge current handling capability	10 single / 5 multiple kA (test pulse 8/20 μ s)		
Residual pulse energy	250 μ J typically (test pulse 4 kV 1.2/50 μ s / 2 kA 8/20 μ s) main path - protected side		

Mechanical Data

Number of matings	500
Weight	45 g

Environmental Data

Operating temperature	-40 °C to +75 °C
Waterproof degree	IP67 (according to IEC 60529, data refer to the coupled state)
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Housing	Brass	Silver / Gold Plating
Port 1 center contact	Brass	Gold Plating (without Nickel underplating)
Port 2 center contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00308588
Instruction	DOC-0000732903

Remarks

ATEX/IEC Marking:
- II 3G Ex nA IIC T6...T5 Gc acc. EN 60079-15
- II 3D Ex tc IIIC T85°C...T100°C Dc acc. EN 60079-31
EU Declaration of Conformity (DoC): DOC-0000731654

Tamb: up to +75 °C for T6/T85°C or +80 °C for T5/T100°C

ATEX RF SPD 9096.26.0601

For RF power of various groups of equipment acc. EN 60079-0 see instruction

For remote powering voltage and current (dc/ac) see instruction

RF requirement for the transmission line connected to the device: VSWR min. 1:1.92 / return loss max. 10 dB

Cable lug for grounding included

⚠ WARNING - DO NOT CONNECT OR DISCONNECT WHEN ENERGIZED!

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

9096.26.0601