

# LOCTITE MR 11

December 2016

## PRODUCT DESCRIPTION

LOCTITE MR 11 provides the following product characteristics:

<b>Technology</b>	Silicone
<b>Appearance</b>	Colorless liquid
<b>Cure</b>	Air dry
<b>Product Benefits</b>	<ul style="list-style-type: none"><li>• Low viscosity</li><li>• Contains solvent</li></ul>
<b>Application</b>	Coating
<b>Application Method</b>	Brush, Dip or Spray

LOCTITE MR 11 liquid silicone mold release is designed for use on epoxies, polyesters and other similar polymer systems. It is formulated to dry to a film after application with exceptional non-stick property that is dry to the touch.

## TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Brookfield 350, ASTM D2393, mPa·s (cP)	350
Density, g/cm <sup>3</sup>	0.68
Shelf Life @ 25°C, months	368
Flash Point, ASTM D93, °C	-4

## TYPICAL CURING PERFORMANCE

### Recommended Drying Conditions

5 to 10 minutes @ 25°C until it is dry to the touch

Care should be taken not to apply the mold release to surfaces assigned to be bonded later.

The above drying profile is a guideline recommendation. Conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer drying equipment.

## GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

## DIRECTIONS FOR USE

1. LOCTITE MR 11 is a flammable material.
2. LOCTITE MR 11 contains solvents therefore proper ventilation should be used.
3. Some substrates may be sensitive to solvents. Testing should be performed before use of LOCTITE MR 11.
4. LOCTITE MR 11 can be applied by brushing, dip coating or spraying.
5. If applying by dipping the entire mold into the mold release, allow excess material to drain prior to drying.
6. A thin film of applied material is more effective than a thick film.
7. Thin layers of build up observed after a large number of applications of mold release material can be removed with the use of Hexane or chlorinated solvents.

## Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

## STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

## Optimal Storage : 25 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

## Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$   
 $\text{kV/mm} \times 25.4 = \text{V/mil}$   
 $\text{mm} / 25.4 = \text{inches}$   
 $\text{N} \times 0.225 = \text{lb}$   
 $\text{N/mm} \times 5.71 = \text{lb/in}$   
 $\text{psi} \times 145 = \text{N/mm}^2$   
 $\text{MPa} = \text{N/mm}^2$   
 $\text{N} \cdot \text{m} \times 8.851 = \text{lb} \cdot \text{in}$   
 $\text{N} \cdot \text{m} \times 0.738 = \text{lb} \cdot \text{ft}$   
 $\text{N} \cdot \text{mm} \times 0.142 = \text{oz} \cdot \text{in}$   
 $\text{mPa} \cdot \text{s} = \text{cP}$

## Disclaimer

### Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

### **In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:**

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

### **In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

### **In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

**Trademark usage:** [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1189029](#)