

LOCTITE M 2016RS E&C

December 2016

PRODUCT DESCRIPTION

LOCTITE M 2016RS E&C provides the following product characteristics:

Technology	Thermosetting
Appearance	Black
Product Benefits	<ul style="list-style-type: none"> One component Applicable with manual or semi automatic screen printing equipment Good screen residence time Can be mixed to produce accurately controlled resistance values Less than 5% resistance changes after soldering, humidity and thermal ageing exposure
Cure	Heat cure
Application	Conductive Ink
Typical Assembly Applications	Printed resistors and Potentiometers
Key Substrates	FR-3, FR-4, CEM-1 and CEM-3 polyether sulphone and ceramic substrates

LOCTITE M 2016RS E&C of products are specifically designed for printing potentiometers and resistors onto printed circuit boards.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity 35,000, mPa·s (cP)	35,000
Density, kg/cm ³	1,340
Shelf Life @ 18 to 25°C (from date of qualification in original seal), year	1
Flash Point, °C	78

TYPICAL SCREEN PRINTING PROCESS

Emulsion Thickness	
Direct or indirect emulsion, µm	25 to 50
Printing Equipment Type	
Manual	
Semi-automatic	
Recommended Screen Type	
Monofilament polyester & Stainless Steel threads/cm	77 to 100
Recommended Squeegee	
Polyurethane, Shore Hardness	60 to 70
Speed (not to exceed), cm/s	10
Applied Dry Coating Thickness	
Applied Dry Coating Thickness, µm	15 to 25

TYPICAL DRYING CYCLE

15 to 30 minutes @ 25 °C:

TYPICAL CURING PERFORMANCE

Convection Box Oven

30 minutes @ 200°C

Infrared Heat Source

6 minutes @ 200°C

If different resistors are applied on the same board, it is not advisable to cure each resistor type individually. It is recommended to dry each resistor after printing, 5 to 10 minutes @ 120°C. Full cure at 200°C should be performed after printing the last resistor type.

These cure schedules are a general guideline for additive circuitry. Other cure schedules can be utilized depending on laminates and processing parameters.

The above cure profile is a guideline recommendation. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

As a cured coating

Physical Properties

Adhesion, ASTM 3359 Method B, grade 5B

Electrical Properties

Resistivity, ±15%, ohms/square/25 µm	>500,000
Temperature Coefficient of Resistance (TCR), ppm	200

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

DIRECTIONS FOR USE

- LOCTITE M 2016RS E&C should be thoroughly stirred prior to use. Avoid rapid stirring as this causes air entrapment..
- Should thinning become necessary, dilute (not to exceed) 1% by weight with butyl carbitol.

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Store in a cool, well ventilated area.

Optimal Storage : 18 to 25 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions $(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$ $\text{kV/mm} \times 25.4 = \text{V/mil}$ $\text{mm} / 25.4 = \text{inches}$ $\text{N} \times 0.225 = \text{lb}$ $\text{N/mm} \times 5.71 = \text{lb/in}$ $\text{psi} \times 145 = \text{N/mm}^2$ $\text{MPa} = \text{N/mm}^2$ $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$ $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$ $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$ $\text{mPa}\cdot\text{s} = \text{cP}$ **Disclaimer****Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 0.2

Americas
+1.888.943.6535

Europe
+32.1457.5611

Asia
+86.21.3898.4800

For the most direct access to local sales and technical support visit: www.henkel.com/electronics

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1239188](#)