

HUBER+SUHNER® DATA SHEET

Coaxial Cable Connector: 11_BNO-0-4-1/133_N

Rev.: E



Description

Straight cable plug

Interface Standards
IEC 60169-22



Technical Data

Electrical Data

Impedance not defined Ω
Interface frequency max. 0.2 GHz

Mechanical Data

Centre contact soldered
Outer contact crimped
Weight 0.0177 kg

Environmental Data

Operating Temperature -50 °C to 125 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium / Brass
Outer contact	Brass
Body	Brass
Insulator	ETFE
Coupling nut	Brass
Gasket	MVQ (Silicone Rubber)
Crimp ferrule	Copper

Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00006181
Catalogue drawing	DOU-00006183
Assembly instruction	DOC-0000179394

Ordering Information

Single package	11_BNO-0-4-1/133_NE
Bulk 100 pcs package	11_BNO-0-4-1/133_NH

Additional Information

Suitable cable	RG_108_AU
----------------	-----------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[11_BNO-0-4-1/133_NE](#)