

LOCTITE® STYCAST CC 8555

August 2023

PRODUCT DESCRIPTION

LOCTITE® STYCAST CC 8555 provides the following product characteristics:

Technology	Urethane acrylate
Appearance	Clear liquid
Components	One component
Fluorescence	Positive under UV light
Product benefits	<ul style="list-style-type: none"> • UV curable • Room temperature moisture cure for shadowed areas • One component • VOC/Solvent free • Good moisture resistance • Excellent chemical resistance • Good wettability and void free
Application	Conformal coating
Operating temperature, °C	-40 to 130
Key substrates	<ul style="list-style-type: none"> • Variety of metal surface • Ceramic • Glass filled epoxy

LOCTITE® STYCAST CC 8555 is a conformal coating designed to provide rugged protection from moisture and harsh chemicals. It is compatible with industry standard solder masks, no-clean fluxes, metallization, components and substrate materials.

LOCTITE® STYCAST CC 8555 conformal coating is specifically formulated to rapidly gel and immobilize when exposed to UV light and then fully cure when exposed to atmospheric moisture, ensuring optimum performance even in shadowed areas.

LOCTITE® STYCAST CC 8555 has a V0 rating per UL 94 and has a Relative Temperature Index (RTI) rating of 130°C per UL 746E. This product conforms to IPC-CC-830 requirements as well.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity @ 25°C, mPa.s (cP)	60
Specific gravity @ 25°C, g/cc	1.05
Shelf life @ 25°C, days	365
Flash point - see SDS	

TYPICAL CURING PERFORMANCE

Recommended UVA cure condition

Medium pressure mercury vapor lamp:

Wavelength, nm	365
Exposure time, seconds	30
Light intensity, mW/cm ²	300 to 600

Moisture cure for shadowed areas

Relative humidity 50%, @ 25°C, hours	72
--------------------------------------	----

The above cure profile is a guideline recommendation. Cure rate and ultimate depth of cure depend on light intensity, spectral distribution of light source, exposure time and the light transmittance of the substrate.

Areas hidden or shadowed from the UV light source will moisture cure at ambient temperature and humidity. No further processing is necessary.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Hardness, Shore A @ 20s	77
-------------------------	----

Electrical properties

Volume resistivity @ 25°C, ohm-cm	1.46×10 ¹⁴
Surface resistivity @ 25°C, ohm	1.27×10 ¹⁴
Dielectric strength, kV/mm	27.5
Dielectric constant @1 MHz	2.51
Dissipation factor @1 MHz	0.057

Miscellaneous

Tensile strength, N/mm ² (psi)	10.4 (1,510)
Tensile elongation at break, %	31

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet (SDS).

Directions for use

1. Surface preparation of assembled boards prior to applying LOCTITE® STYCAST CC 8555 is not required. However, keeping the board surface clean and dry is recommended. Improved adhesion and reliability performance can be achieved when contaminants such as ionic, dust, salts and oils are cleaned from the assembled board.
2. Final coating thickness is influenced by board size, part geometry and application method.
3. **Spray and flow coating operations:** Solventless conformal coatings usually require modified operating procedures compared to solvent-based systems such as lower flow rate through the gun, increased atomization pressure to create a fine mist and spray gun location approximately 2 to 3 inches above the assembled board.
4. Equipment parameters such as nozzle design, nozzle orientation, path speed and number of passes will impact final coating thickness.

Storage:

Store product in an unopened container in a dry location. Storage information may be indicated on the product container labeling.

Storage between 18-26°C, out of sunlight and in original unopened containers. Refer to packaging specific quote for shelf-life information. Once opened, containers should be purged with dry nitrogen.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on the specifications of this product.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer

The information provided in this Technical Data Sheet (TDS) including there commendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage:

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[2880013](#) [2962044](#) [3021516](#) [2998195](#)