

# LOCTITE STYCAST US 1000

March 2022

## PRODUCT DESCRIPTION

LOCTITE STYCAST US 1000 provides the following product characteristics:

<b>Technology</b>	Polyurethane
Appearance - Part A	Black paste
Appearance - Part B	Brown liquid
Appearance (cured)	Dark grey
Components	Two components - requires mixing
Mix Ratio by volume: Part A: Part B	100 : 15
Mix Ratio by weight: Part A: Part B	100 : 11
<b>Cure</b>	Room temperature cure and Heat cure
Product Benefits	<ul style="list-style-type: none"> <li>• Low viscosity</li> <li>• Easy mix ratio</li> <li>• Fast gel time</li> <li>• Designed for automated dispensers</li> </ul>
<b>Application</b>	Potting and Encapsulating
Typical Assembly Applications	Electrical component encapsulation & potting
Operating Temperature	-40 to +125 °C

LOCTITE STYCAST US 1000 is a flexible, flame retardant, mineral filled 2-component polyurethane compound. This potting compound has low viscosity, flows well, and adheres to many substrates.

## TYPICAL PROPERTIES OF UNCURED MATERIAL

### Part A Properties

Density, g/cm <sup>3</sup>	1.7
Viscosity @ 25°C, mPa·s (cP): @ Shear rate of 15 s <sup>-1</sup>	20,000
Shelf Life @ 18 to 25°C, days	365

### Part B Properties

Density, g/cm <sup>3</sup>	1.2
Viscosity @ 25 °C, mPa·s (cP): @ Shear rate of 15 s <sup>-1</sup>	200
Shelf Life @ 18 to 25°C, days	365

## Mixed Properties

Density, g/cm <sup>3</sup>	1.6
Viscosity @ 25 °C, mPa·s (cP): @ Shear rate of 15 s <sup>-1</sup>	17,500
Pot Life @ 25°C, minutes	4 to 8

## TYPICAL CURING PERFORMANCE

### Recommended Cure Schedule

2 hours @ 65°C

### Alternate Cure Schedule

48 hours @ 25°C or

1 hour @ 80°C or

1 hour @ 100°C

The above cure profile(s) are guideline recommendation(s). These conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

## TYPICAL PROPERTIES OF CURED MATERIAL

### Physical Properties

Hardness, Shore A	85
Elongation, %	20
Tensile Strength	N/mm <sup>2</sup> 4 (psi) (580)

Glass Transition Temperature, (Tg) by TMA, °C 10 to 25

Coefficient of Thermal Expansion, ppm/K:

Below Tg	40 to 50
Above Tg	160 to 180

Thermal Conductivity, W/(m·K) 0.6

Flammability @ 6 mm, UL94 V-0

### Electrical Properties

Volume Resistivity, ohm-cm	3.2×10 <sup>15</sup>
Surface Resistivity, ohm-cm	8.1×10 <sup>14</sup>
Dielectric Constant @ 1 MHz	4.1
Dielectric Strength, kV/mm	25

## GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

**Directions for use**

1. Part B is sensitive to moisture. Do not expose to humid conditions. Keep in closed containers or vessels as much as possible.
2. Allow products to reach 18 to 25°C before use to ensure proper processing of the materials.
3. Moderate filler settling can occur in Part A during storage. Before use, stir gently to make it homogeneous again.
4. Substrates should be free of contaminants such as dust, moisture and oils which can cause poor adhesion.
5. Accurately weigh Part A and Part B in the recommended ratio.
6. To ensure a void-free embedment, vacuum de-airing should be used to remove any entrapped air introduced during the mixing operation.
7. Cure product with the recommended cure schedule.

**STORAGE**

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

**Optimal Storage: 10 to 30°C. Storage below 10°C or above 30°C can adversely affect product properties.**

**Frost Sensitive: Yes, (Component B)**

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel Representative.

**Conversions**

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$   
 $\text{kV/mm} \times 25.4 = \text{V/mil}$   
 $\text{mm} / 25.4 = \text{inches}$   
 $\text{N} \times 0.225 = \text{lb/F}$   
 $\text{N/mm} \times 5.71 = \text{lb/in}$   
 $\text{N/mm}^2 \times 145 = \text{psi}$   
 $\text{N/mm}^2 = \text{MPa}$   
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$   
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$   
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$   
 $\text{mPa}\cdot\text{s} = \text{cP}$

**Disclaimer**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:**

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

**In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

**Trademark usage**

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

**Reference 1**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[2583477](#)