

Sencity Road Antenna K5022222

Description

Broadband antenna in fiberglass radome.
Gain dB 0 (ref. to the quarter-wave antenna).



Product Configuration

Technical Data

Electrical Data

	Band 1
Band Name	2M Band
Frequency (MHz)	152 - 178
VSWR	1.4
Impedance (Ohm)	50
Composite power max (W)	100
Ambient temperature (°C)	50

Ports

	Port 1
Port name	2M Band
Connector	UHF, jack (female)
Polarization	vertical
DC grounded	Yes

Connections

	Band 1
Port 1	X

General Data

Requires mounting on a conductive surface 1.0 x 2.0 m minimum with 3 studs M10 and counterflange.
Recommended torque: 14 Nm.
Note: No superstructures in this area.

Mechanical Data

Dimensions (mm)	225 x 252 x 126 (Height x Width x Depth)
Weight (kg)	1.2

Radiator and Base: Aluminum.
Radome: Fiberglass, colour: Grey.
Studs and all screws and nuts: Stainless steel.
Sealing: Neoprene and polyurethane.
Note: Don't use detergents that might harm the sealing.

DC grounded to protect against lightning and high-tension lines.

Packaging size (outside): 260 x 260 x 130 mm

Sencity Road Antenna K5022222

Environmental Data

Environmental conditions	outdoor
Operation temperature (°C)	-40 to 85
Storage temperature (°C)	-55 to 85
IP rating	IP66
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
WEEE 2012/19/EU	no special marking needed
REACH 1907/2006/EC	compliant

Material Data

Radome colour	grey
Back plate/base plate colour	black
Back plate/base plate material	Aluminium

Related Documents

Painting instruction	DOC-0000256180
Security instruction	DOC-0000278984
3D-model	DOC-0000862887

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

K5022222