

HIGH PERFORMANCE

conga-TS67




- COM Express Type 6
- Based on 2nd Generation Intel® Core™ low-power processors
- Soldered CPUs for higher shock resistance
- High end graphics performance
- Intel® Turbo Boost Technology 2.0

COM  **Express®**

Formfactor	COM Express™ Basic (95 x 125 mm) Type 6 Connector Layout				
CPU	Intel® Celeron™ 807UE	1x 1.0GHz	1MB L3 cache	1333MT/s	TDP 10 W
	Intel® Celeron™ 827E	1x 1.4GHz	1.5MB L3 cache	1333MT/s	TDP 17 W
	Intel® Celeron™ 847E	2x 1.1GHz	2MB L2 cache	1333MT/s	TDP 17 W
	Intel® Core™ i3-2340UE	2x 1.3GHz	3MB L2 cache	1333MT/s	TDP 17 W
	Intel® Core™ i7-2610UE	2x 1.5GHz	3MB L2 cache	1333MT/s	TDP 17 W
	Intel® Core™ i7-2655LE	2x 2.2GHz	4MB L2 cache	1333MT/s	TDP 25 W
	Intel® Turbo Boost Technology 2.0 Intel® Hyper-Threading Technology Integrated dual channel memory controller up to 25.6 GByte/sec. memory bandwidth Integrated Intel® HD Graphics 3000 with dynamic frequency up to 1.2GHz Intel® Clear Video HD Technology				
DRAM	2 Sockets SO-DIMM DDR3 up to 1600MT/s and 16 GByte				
Chipset	Mobile Intel® 6 Series Chipset: Intel® QM67 / Intel® HM65 (Intel® Celeron™ version)				
Ethernet	Intel® 82579 GbE LAN Controller with AMT 7.0 support				
I/O Interfaces	7x PCI Express™ GEN. 2.0 lanes 1x PEG 2x Serial ATA® with 6 Gb/s 2x Serial ATA® with 3 Gb/s (AHCI) RAID 0/1/5/10 support (QM67 only) 2x ExpressCard® 8x USB 2.0 (EHCI) LPC bus I²C bus (fast mode / 400 kHz / multi-master)				
Sound	Digital High Definition Audio Interface with support for multiple audio codecs				
Graphics	Intel® Flexible Display Interface (FDI) OpenGL 3.0 and DirectX10.1 support Two independent pipelines for full dual view support optional High performance hardware MPEG-2 decoding WMV9 (VC-1) and H.264 (AVC) support Blu-ray support @ 40 MBit/s hardware motion compensation				
LVDS	Dual channel LVDS transmitter Supports flat panels 2x24 Bit interface VESA mappings resolutions up to 1920x1200 Automatic Panel Detection via EDID/EPI				
Digital Display Interface	1x SDVO / DisplayPort 1.1 / TMDS (DVI / HDMI) 2x DisplayPort 1.1 / TMDS (DVI HDMI)				
CRT Interface	350 MHz RAMDAC resolutions up to QXGA (2048x1536)				
congatec Board Controller	Multi Stage Watchdog non-volatile User Data Storage Manufacturing and Board Information Board Statistics BIOS Setup Data Backup I²C bus (fast mode / 400 kHz / multi-master) Power Loss Control				
Embedded BIOS Features	AMI Aptio® UEFI 2.x firmware 8 MByte serial SPI firmware flash High Accessible Program (HAP)				
Security	The conga-TS67 can be optionally equipped with a discrete "Trusted Platform Module" (TPM). It is capable of calculating efficient hash and RSA algorithms with key lengths up to 2,048 bits and includes a real random number generator. Security sensitive applications such as gaming and e-commerce will benefit also with improved authentication integrity and confidence levels.				
Power Management	ACPI 4.0 with battery support				
Operating Systems	Microsoft® Windows 8 Microsoft® Windows 7 Linux Microsoft® Windows® embedded Standard				
Power Consumption	Typ. application: tbd. see manual for full details CMOS Battery Backup				
Temperature	Operating: 0 .. +60°C Storage: -20 .. +80°C				
Humidity	Operating: 10 - 90% r. H. non cond. Storage: 5 - 95% r. H. non cond.				
Size	95 x 125 mm (3.74" x 4.92")				

conga-TS67 | Block diagram



conga-TS67 | Order Information

Article	PN	Description
conga-TS67/i7-2655LE	046401	Intel® Core™ i7-2655LE dual core processor with 2.2GHz 4MB L3 cache and 1333MT/s dual channel DDR3 memory interface
conga-TS67/i7-2610UE	046402	Intel® Core™ i7-2610UE dual core processor with 1.5GHz 3MB L3 cache and 1333MT/s dual channel DDR3 memory interface
conga-TS67/i3-2340UE	046403	Intel® Core™ i3-2340UE dual core processor with 1.3GHz 3MB L3 cache and 1333MT/s dual channel DDR3 memory interface
conga-TS67/847E	046404	Intel® Celeron® 847E dual core processor with 1.1GHz 2MB L3 cache and 1333MT/s dual channel DDR3 memory interface
conga-TS67/827E	046405	Intel® Celeron® 827E single core processor with 1.4GHz 1.5MB L3 cache and 1333MT/s dual channel DDR3 memory interface
conga-TS67/807UE	046406	Intel® Celeron® 807UE single core processor with 1.0GHz 1MB L3 cache 1333MT/s single channel DDR3 memory interface and no PEG Port
conga-TS67/HSP-HP-B	046450	Standard heatspreader for high performance COM Express modules conga-TS67 and TS77 with integrated heat pipes. All standoffs are with 2.7mm bore hole
conga-TS67/HSP-HP-T	046451	Standard heatspreader for high performance COM Express modules conga-TS67 and TS77 with integrated heat pipes. All standoffs are M2.5mm thread
conga-TS67/CSP-HP-B	046452	Standard passive cooling solution for high performance COM Express modules conga-TS67 and TS77 with integrated heat pipes 15mm silver fins and 20mm overall heat sink height. All standoffs are with 2.7mm bore hole
conga-TS67/CSP-HP-T	046453	Standard passive cooling solution for high performance COM Express modules conga-TS67 and TS77 with integrated heat pipes 15mm silver fins and 20mm overall heat sink height. All standoffs are M2.5mm thread
conga-TS67/CSA-HP-B	046454	Standard active cooling solution for high performance COM Express modules conga-TS67 and TS77 with integrated heat pipes 15mm silver fins 20mm overall heat sink height and integrated 12V fan. All standoffs are with 2.7mm bore hole
conga-TS67/CSA-HP-T	046455	Standard active cooling solution for high performance COM Express modules conga-TS67 and TS77 with integrated heat pipes 15mm silver fins 20mm overall heat sink height and integrated 12V fan. All standoffs are M2.5mm thread
DDR3L-SODIMM-1600 (2GB)	068755	DDR3L SODIMM memory module with 1600 MT/s (PC3L-12800S) and 2GB RAM
DDR3L-SODIMM-1600 (4GB)	068756	DDR3L SODIMM memory module with 1600 MT/s (PC3L-12800S) and 4GB RAM
DDR3L-SODIMM-1600 (8GB)	068757	DDR3L SODIMM memory module with 1600 MT/s (PC3L-12800S) and 8GB RAM

Accessories

conga-TEVAL	065800	Evaluation carrier board for Type 6 COM-Express-modules
conga-LDVI/EPI	011115	LVDS to DVI converter board for digital flat panels with onboard EEPROM
COM-Express-carrier-board-Socket-5	400007	Connector for COM-Express carrier boards height 5mm packing unit 4 pieces
COM-Express-carrier-board-Socket-8	400004	Connector for COM-Express carrier boards height 8mm packing unit 4 pieces

© 2016 congatec AG. All rights reserved.

All data is for information purposes only. Although all the information contained within this document is carefully checked, no guarantee of correctness is implied or expressed. Product names, logos, brands, and other trademarks featured or referred are the property of their respective trademark holders. These trademark holders are not affiliated with congatec AG. Rev. July 12, 2015 KS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[congatec:](#)

[CONGA-TS67/CSA-HP-T](#) [CONGA-TS67/CSP-HP-T](#) [CONGA-TS67 HSP-HP-B](#) [CONGA-TS67 HSP-HP-T](#) [CONGA-TS67/807UE](#) [CONGA-TS67/827E](#) [CONGA-TS67/I7-2655LE](#) [CONGA-TS67/847E](#) [CONGA-TS67/B810E](#) [CONGA-TS67/CSA-HP-B](#) [CONGA-TS67/CSP-HP-B](#) [CONGA-TS67/I3-2340UE](#) [CONGA-TS67/I7-2610UE](#)