

LOCTITE STYCAST 2075

August 2018

PRODUCT DESCRIPTION

LOCTITE STYCAST 2075 provides the following product characteristics:

Technology (Part A)	Epoxy
Technology (Part B)	Amine
Components	Two components - requires mixing
Appearance, Resin (Part A)	Black liquid
Appearance, Hardener (Part B)	Amber liquid
Mix Ratio by weight: Part A: Part B	100 : 6.5 to 7.0
Mix Ratio by volume: Part A: Part B	100 : 11 to 12
Product Benefits	<ul style="list-style-type: none"> • Low viscosity • High gloss • Non-abrasive filler • Good air release properties
Cure	Room temperature and Heat cure
Application	Encapsulation, Potting
Operating Temperature	-40 to 130°C

LOCTITE STYCAST 2075 is a general purpose encapsulant is formulated using non-abrasive fillers that is ideal for automatic meter/mix equipment dispensing.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Part A Properties

Viscosity, Brookfield , 25 °C, mPa·s (cP)	22,500
Density, g/cm ³	1.7
Shelf Life @ 25°C, days	365

Part B Properties

Viscosity, Brookfield , 25 °C, mPa·s (cP)	75
Density, g/cm ³	0.97
Shelf Life @ 25°C, days	365

Mixed Properties

Viscosity, Brookfield , 25 °C, mPa·s (cP)	6,800
Density, g/cm ³	1.62
Work Life (100 g mass) @ 25 °C, minutes	45
Shelf Life @ 25°C, days	365
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE

Cure Schedule

24 hours @ 25°C
8 to 16 hours @ 45°C
2 to 4 hours @ 65°C

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Hardness, Shore D	81
Thermal Conductivity, W/(m·K)	0.62
Coefficient of Linear Thermal Expansion , TMA 10 ⁻⁶ /°C	70
Linear Shrinkage, cm/cm	0.004

Electrical Properties

Volume Resistivity @ 25°C, ohm-cm	>10 ¹⁵
Dielectric Constant @ 1mHz	5.0
Dissipation Factor @ 1mHz	0.025
Dielectric Strength, V/mil	400

TYPICAL PERFORMANCE OF CURED MATERIAL

Miscellaneous:

Flexural Strength	N/mm ² 62 (psi) (9,000)
Compressive Strength	N/mm ² 103 (psi) (15,000)
Tensile Strength	N/mm ² 41 (psi) (6,000)

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

DIRECTIONS FOR USE

1. To ensure the long term performance of the potted or encapsulated electrical / electronic assembly, complete cleaning of the substrates should be performed to remove contamination such as dust, moisture, salt, and oils which can cause electrical failure, poor adhesion or corrosion in an embedded part.
2. Some filler settling is common during shipping and storage. For this reason, it is recommended that the contents of the shipping container be thoroughly mixed prior to use. Power mixing is preferred to ensure homogeneous product.
3. Accurately weigh resin and hardener into a clean container in the recommended ratio. Weighing apparatus having an accuracy in proportion to the amounts being weighed should be used.
4. Blend components by hand, using a kneading motion, for 2 to 3 minutes. Scrape the bottom and sides of the mixing container frequently to produce a uniform mixture. If possible, power mix to an additional 2 to 3 minutes. Avoid high mixing speeds which could entrap excessive amounts of air or cause overheating of the mixture resulting in reduced working life.
5. To ensure a void-free embedment, vacuum deairing or degassing should be performed to remove any entrapped air introduced during the mixing operation.
6. Pump-down or pull vacuum on the mixture to achieve an ultimate vacuum or absolute pressure of 1 to 5 torr or mm Hg. The foam will rise several times in the liquid height and then subside.
7. Continue vacuum deairing until most of the bubbling has ceased. This usually takes 3 to 10 minutes.
8. To facilitate deairing in difficult to deair materials, add 1 to 3 drops of an air release agent, such as ANTIFOAM 88 into 100 grams of mixture.
9. Gentle warming will also help, but working life will be shortened.
10. Pour mixture into cavity or mold. Gentle warming of the mold or assembly reduces the viscosity. This improves the flow of the material into the unit having intricate shapes or tightly packed coils or components. Further vacuum deairing in the mold may be required for critical applications.

STORAGE:

Store in original, tightly covered containers in clean, dry areas. Storage information may be indicated on the product container labeling.

Optimal Storage: 25°C. Storage below 25°C or greater than 25°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$

$\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N} \cdot \text{m} \times 8.851 = \text{lb} \cdot \text{in}$
 $\text{N} \cdot \text{m} \times 0.738 = \text{lb} \cdot \text{ft}$
 $\text{N} \cdot \text{mm} \times 0.142 = \text{oz} \cdot \text{in}$
 $\text{mPa} \cdot \text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Loctite:

[1188023](#) [1188025](#) [1188026](#) [2055088](#)