

**Technical Data Sheet** 

# **LOCTITE STYCAST ES 1002**

November 2021

## PRODUCT DESCRIPTION

LOCTITE STYCAST ES 1002 provides the following product characteristics:

Technology	Ероху
Appearance,Resin	Black
(Component A)	
Appearance, Hardener	Tan
(Component B)	
Appearance (cured)	Black
Components	Two components - requires mixing
Mix Ratio by volume:	1:1
Part A: Part B	
Mixing Ratio,	100 : 100
by weight	
Component A:	
Component B	
Cure	Room Temperature or Heat Cure
Application	Potting and Encapsulating

LOCTITE STYCAST ES 1002 is a two-component casting system with excellent handling properties. This low cost, flexible system is filled with a non-abrasive filler for machine metering/dispensing or regular hand mixer applications.

## TYPICAL PROPERTIES OF UNCURED MATERIAL

Part A Properties	
Viscosity, Brookfield - RVF, cP: Spindle 6, speed 2 rpm Spindle 6, speed 20 rpm	55,000 28,000
Density, @ 25°C, g/cm <sup>3</sup>	1.57
Filler Content, %	50
Solids Content, %	100
Part B Properties	
Viscosity, Brookfield - RVF, cP:	
Spindle 5, speed 20 rpm	6,300
Density, @ 25°C, g/cm <sup>3</sup>	1.48
Filler Content, %	60
Solids Content, %	100
Mixed Properties	
Viscosity, Brookfield - RVF, cP: Spindle 4, speed 20 rpm	19,500
Density, @ 25°C, g/cm <sup>3</sup>	1.55
Peak Exotherm Temperature, °C: 200 g mass	90
Pot Life @ 25°C, minutes: 200 g mass	60
Gel Time @ 25°C, hours	5
Flash Point - See SDS	

# TYPICAL CURING PERFORMANCE Recommended Cure Schedule

36 to 48 hours @ 25°C

### Alternate Cure Schedule

3 hours @ 60°C

The above cure profile is a guideline recommendation. These cure conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

### **TYPICAL PROPERTIES OF CURED MATERIAL**

#### **Physical Properties :**

Coefficient of Thermal Expansion, ppm/°C:		
Below Tg	66	
Above Tg	150	
Glass Transition Temperature(Tg), °C		
Coefficient of Thermal Conductivity, W/(m-K) 0.644		644
Linear Shrinkage, %	0.1	
Shore Hardness, Durometer D 88		
Water Absorption, %:		
24 hours	0.32	
Water Absorption, 24-hr immersion		
Tensile Elongation, %	6.3	3
Tensile Strength	N/mm² (psi)	18.5 (2.670)
Compressive Strength	N/mm <sup>2</sup> (psi)	81 (11,700)
Flexural Strength	N/mm² (psi)	34.3 (4,975)
Tear Strength	N/mm² (psi)	1.7 (240)

#### **Electrical Properties:**

Dielectric Strength, 10 mil thickness, volts/mil	1,135
Volume Resistivity, ohm-cm	6.38×10 <sup>14</sup>
Volume Resistivity, ohm-cm @ 105°C	9.28×10 <sup>10</sup>
Surface Resistivity, ohms @ 25°C	2.12×10 <sup>15</sup>
Surface Resistivity, ohms @ 105°C	6.65×10 <sup>15</sup>
Dielectric Constant / Dissipation Factor @ 25°C:	
100 Hz	4.7 / 0.04
1 kHz	4.6 / 0.03
10 kHz	4.4 / 0.02
100 kHz	4.2 / 0.02
Dielectric Constant / Dissipation Factor @ 105°C:	
100 Hz	22.2 / 1.3
1 kHz	8.6 / 0.3
10 kHz	7.7 / 0.09
100 kHz	7.0 / 0.09



#### GENERAL INFORMATION For safe handling information on this product, consult the Safety Data Sheet, (SDS).

#### Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

**Note:** Before using this product please purge approximately 30 ml. of material prior to application. Discard purged material in accordance with the Material Safety Data Sheet. A video instruction is available upon request.

#### STORAGE

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

# Optimal Storage: 20 °C to 30 °C. Storage below 20 °C or greater than 30 °C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel Representative.

#### Conversions

 $(^{\circ}C x 1.8) + 32 = ^{\circ}F$ kV/mm x 25.4 = V/mil mm / 25.4 = inches N x 0.225 = lb/F N/mm x 5.71 = lb/in psi x 145 = N/mm<sup>2</sup> MPa = N/mm<sup>2</sup> N·m x 8.851 = lb·in N·m x 0.738 = lb·ft N·mm x 0.142 = oz·in mPa·s = cP

#### Disclaimer

Reference 3

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Loctite: 904609 1084387 2264261