

LOCTITE STYCAST ES 6026

August 2020

PRODUCT DESCRIPTION

LOCTITE STYCAST ES 6026 provides the following product characteristics:

Technology	Epoxy
Appearance - Mixed	Black
Components	Two components - requires mixing
Mix Ratio, by weight - Resin : Hardener	100 : 20
Mix Ratio, by volume - Resin : Hardener	3.1 : 1
Product Benefits	<ul style="list-style-type: none"> • Non-conductive • Low stress • Low shrinkage • High thermal conductivity • Passes NASA outgassing • Low viscosity • Long gel time
Cure	Room temperature cure
Application	Potting and Encapsulating

LOCTITE STYCAST ES 6026 is a two component, high performance epoxy system. This material is formulated to provide low stress and low shrinkage during cure to prevent cracking of ferrite components, while providing superior thermal shock resistance.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Part A Properties

Shelf Life - Refer to package label for proper storage condition

Part B Properties

Shelf Life - Refer to package label for proper storage condition

Mixed Properties

Specific Gravity, mixed	1.73
Mixed Viscosity, mPa·s (cP):	
@ 25°C	7,000
@ 85 °C	550
Work Life, 50 gram mass, minutes:	
@ 121°C	15
@ 100 °C	60

TYPICAL CURING PERFORMANCE

Gel Time

Gel Time, 50 gram mass, minutes:	
@ 100°C	90
@ 121 °C	30 to 40

Recommended Curing Conditions

6 hours @ 82 °C + post cure at operating temperature of 4 hours

Alternate Cure Schedule

16 to 20 hours @ 82°C or
4 to 6 hours @ 100°C + a post cure of 2 hours @ 121°C or
4 hours @ 121°C

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Hardness, Shore D	95
Thermal Conductivity, W/(m·K)	0.634
Elongation, %	1.7
Linear Shrinkage, in/in	0.006
Moisture Absorption, %	0.01

Electrical Properties

Volume Resistivity, ohm-cm	1.8×10 ¹⁶
Dielectric Constant / Dissipation Factor :	
@ 100 Hz	4.1/0.005
@ 1 KHz	4.1/0.005
@ 100 KHz	4.0/0.008
Dielectric Strength, volts/mil	1,010

Adhesive Properties

Compressive Strength	N/mm ² 126.79
	(psi) (18,390)
Tensile Strength	N/mm ² 36.54
	(psi) (5,300)

TYPICAL PERFORMANCE OF CURED MATERIAL

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

DIRECTIONS FOR USE

1. Pre-mix resin and pre-mix hardener separately.
2. Weigh the above resin and hardener into a clean container, and mix until a uniform color.
3. Pour mixture into another clean container, and mix for 30 seconds.
4. Use low speed mixing to reduce air entrapment. If air bubbles persist, place under vacuum.
5. Cure mixture according to above cycle. Cure time is measured after the product reaches curing temperature.
6. Should crystallization appear in hardener 027, warm container to 65°C to remelt crystals. Usually, 2 hours in a circulating air oven is sufficient for complete melting.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Liquid Storage - Liquids should be stored at 25°C or below, in closed containers. If stored below 25°C, the material MUST be allowed to come to room temperature, in the sealed container, to avoid moisture contamination.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb/F}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N} \cdot \text{m} \times 8.851 = \text{lb} \cdot \text{in}$
 $\text{N} \cdot \text{m} \times 0.738 = \text{lb} \cdot \text{ft}$
 $\text{N} \cdot \text{mm} \times 0.142 = \text{oz} \cdot \text{in}$
 $\text{mPa} \cdot \text{s} = \text{cP}$

Disclaimer

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Loctite:

[2228731](#) [232528](#) [235988](#) [530062](#) [538401](#)