

TECHNOMELT PA 668 N

June 2021

PRODUCT DESCRIPTION

TECHNOMELT PA 668 N provides the following product characteristics:

Technology	Polyamide
Appearance	Clear
Application	Molding compound thermoplastic
Cure	Physical setting
Operating Temperature	-25 to +105 °C
Typical Applications	Encapsulation

TECHNOMELT PA 668 N is used for molding applications where optical transparency is required.

TYPICAL MATERIAL PROPERTIES

Physical Properties

Density, g/cm ³	0.98
Softening Point, °C	155
ASTM E28 (in glycerine)	
Viscosity @ 225°C, mPa·s (cP)	5,500
ASTM D-3236, RVT, Spindle 27	
Hardness, Shore A	90
ISO 868/15s	
Elongation, %	600
ISO 527, Specimen No. 5	
Cross-head-speed: 50mm/min	
Cold Flex Temperature, °C	-25

TYPICAL MATERIAL PERFORMANCE

Performance:

Yield Strength	5.5
ISO 527, Specimen no. 5	
Cross-head-speed: 50mm/min	
Break Strength	8.5
ISO 527, Specimen no. 5	
Cross-head-speed: 50mm/min	

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

Pretreatment:

The substrate should be clean, dry, free of dust, oil, grease and other contaminants.

Application:

Application Temperature: 180 to 230°C

Application System: Hot Melt Application System

When bonding to a substrate with high thermal conductivity the use of a specific application temperature is required for good wetting. Do not heat the product above the specified application temperature range.

When the product is not in use do not apply heat, this will degrade the quality of the product and in extreme cases cause carbonization. TECHNOMELT PA 668 N may absorb moisture from the air. This will not be apparent in the solid form, but may cause bubbles on heating and could affect the bond quality. It is important, therefore, that containers are kept closed and sealed when not in use.

Cleaning:

Carbonized and set (non thermoplastic) material must be removed mechanically. Removal of the thermoplastic material from the hot apparatus can be achieved with solvent free cleaning system, such as Technomelt PA 62 (see separate technical information).

TECHNOMELT PA 62 is sold in select regions only. Please consult your local Henkel Sales representative for availability.

Storage:

When properly stored in a cool, dry location, with the container tightly closed when not in use, this product will have a shelf life of at least 24 months.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local Henkel representative for assistance and recommendations on the specifications of this product.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb/F}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.



In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1

Americas
+1.888.943.6535

Europe
+32.1457.5611

Asia
+86.21.2891.8000

For the most direct access to local sales and technical support visit: www.henkel.com/electronics

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1973209](#)