



## Product Description

GRF2012 is a broadband gain block with low noise figure and industry leading linearity designed for small cell, wireless infrastructure and other high performance applications. It exhibits outstanding broadband NF, linearity over 700 to 3800 MHz with a single match.

The device is operated from a supply voltage of 2.7 to 8.0 V with a selectable Iddq range of 15 to 100 mA for optimal efficiency and linearity.

GRF2012 is internally matched to 50  $\Omega$  at the input and output ports, needing only external DC blocks and a bias choke on the output.

Consult with the GRF applications engineering team for custom tuning/evaluation board data and device s-parameters

## Features

Reference: 5V/90mA/900 MHz

- Gain: 14.8 dB
- OIP3: 40.0 dBm
- OP1dB: 23.0 dBm
- NF: 2.7 dB


Reference: 8V/100mA/900 MHz

- Gain: 14.9 dB
- OIP3: 40.0 dBm
- OP1dB: 25.0 dBm
- NF: 2.8 dB

- Flexible Bias
- Internally Matched to 50  $\Omega$
- Process: GaAs pHEMT

## Applications

- High Performance Gain Block
- Linear Driver Amplifier
- Small Cells and Cellular Repeaters
- IF Amplifier





Released

# GRF2012

Broadband Linear Gain Block  
0.05 to 6.0 GHz

## Absolute Ratings:

Parameter	Symbol	Min.	Max.	Unit
Supply Voltage	V <sub>DD</sub>	0	9.0	V
RF Input Power: (Load VSWR < 2:1; V <sub>D</sub> : <= 8.0 volts)	P <sub>IN MAX</sub>		22	dBm
Operating Temperature (Package Heat Sink)	T <sub>AMB</sub>	-40	105	°C
Maximum Channel Temperature (MTTF > 10 <sup>6</sup> Hours)	T <sub>MAX</sub>		170	°C
Maximum Dissipated Power	P <sub>DISS MAX</sub>		1.0	W
<b>Electrostatic Discharge:</b>				
Charged Device Model:	CDM	1500		V
Human Body Model:	HBM	250		V
<b>Storage:</b>				
Storage Temperature	T <sub>STG</sub>	-65	150	°C
Moisture Sensitivity Level	MSL		1	–



**Caution!** ESD Sensitive Device




Exceeding Absolute Maximum Rating conditions may cause permanent damage to the device.

**Note:** For manufacturing information, see the [Guerrilla-RF.com](http://Guerrilla-RF.com) website for the following document located on the GRF2012 landing page: **Manufacturing Note—MN-001 Product Tape and Reel, Solderability and Package Outline Specification.**

[Link to manufacturing note](#)

## Pin Out (Top View)



## Pin Assignments:

Pin	Name	Description	Note
1	V <sub>ENABLE</sub>	Enable Voltage Input	V <sub>ENABLE</sub> and series resistor set I <sub>DDQ</sub> . V <sub>ENABLE</sub> < =0.2 volts disables device. On -die pull-down resistor will turn the part off if this node is allowed to float.
2	NC	No Connect or Ground	No internal connection to die
3	RF_In	LNA RF input	Internally matched 50Ω. An external DC blocking cap must be used.
4	RF_Out	LNA RF output	Internally matched 50Ω. V <sub>DD</sub> must be applied through a choke to this pin
5	NC	No Connect or Ground	No internal connection to die
6	NC	No Connect or Ground	No internal connection to die
PKG BASE	GND	Ground	Provides DC and RF ground for LNA, as well as thermal heat sink. Recommend multiple 8 mil vias beneath the package for optimal RF and thermal performance. Refer to evaluation board top layer graphic on schematic page.



Released

# GRF2012

**Broadband Linear Gain Block**  
**0.05 to 6.0 GHz**

## Nominal Operating Parameters:

Parameter	Symbol	Specification			Unit	Condition
		Min.	Typ.	Max.		
Test Frequency	$F_{TEST}$		900		MHz	$V_{DD} = 5.0\text{ V}$ , $T_A = 25^\circ\text{C}$
Gain	$S_{21}$	13.8	14.8		dB	
Evaluation Board Noise Figure	NF		2.7	2.95	dB	
Output 3rd Order Intercept	OIP3		40.0		dBm	+2.0 dBm $P_{OUT}$ per tone at 2 MHz Spacing (899 and 901 MHz)
Output 1dB Compression Power	OP1dB	21.5	23.0		dBm	
Switching Rise Time	$T_{RISE}$		200		ns	
Switching Fall Time	$T_{FALL}$		300		ns	
Supply Current	$I_{DD}$	80	94	108	mA	$V_{DD}=V_{ENABLE}=5.0\text{V}$ ; $R_{BIAS}: 300\Omega$
Enable Current	$I_{ENABLE}$		5	8	mA	
<b>Disabled Mode</b>						
Leakage Current	$I_{LEAKAGE}$		110	300	uA	$V_{DD}: 5.0\text{V}$ ; $V_{ENABLE}: 0.0\text{V}$
<b>Thermal Data</b>						
Thermal Resistance: (Infra-Red Scan)	$\Theta_{jc}$		55		$^\circ\text{C}/\text{W}$	On standard Evaluation Board
Channel Temperature @ +85 C Reference (Package heat sink)	$T_{CHANNEL}$		110 (see note)		$^\circ\text{C}$	$V_{DD}: 5.0\text{ V}$ ; $I_{DDQ}: 90\text{ mA}$ ; No RF; $P_{DISS}: 450\text{ mW}$

Note: MTTF >10<sup>6</sup> hours for  $T_{CHANNEL} < 170$  degrees C.





Released



# GRF2012

Broadband Linear Gain Block  
0.05 to 6.0 GHz

## GRF2012 Evaluation Board Measured Data vs. Bias: (0.4 to 3.8 GHz Tune)



## GRF2012 Evaluation Board Measured Data vs. Bias: (0.4 to 3.8 GHz Tune)







Released


# GRF2012

Broadband Linear Gain Block  
0.05 to 6.0 GHz


## GRF2012 Evaluation Board S-Pars and Stability Mu Factor: (0.4 to 3.8 GHz Match)



Note: Mu factor  $\geq 1.0$  implies unconditional stability.



GRF2012 Application Schematic (0.7 to 3.8 GHz)



GRF2012 Evaluation Board Assembly Diagram






Released


# GRF2012

**Broadband Linear Gain Block**  
0.05 to 6.0 GHz

## GRF2012 Standard Evaluation Board BOM: (0.7 to 3.8 GHz Tune)


Component	Type	Manufacturer	Family	Value	Package Size	Substitution
M2	Capacitor	Murata	GRM	100 pF	0402	ok
M5 (See curves)	Resistor	Various	5%	Sets Iddq	0402	ok
M8	Capacitor	Murata	GRM	0.1 uF	0402	ok
M10	Inductor	Murata	LQG	47 nH	0402	ok
M12	Capacitor	Murata	GRM	1000 pF	0402	ok
Evaluation Board	GRF400X_RevC					






Dimensions in millimeters


## 1.5 mm DFN-6 Suggested PCB Footprint (Top View)



Top View



Bottom View



Side View


Dimensions (MM)	
A	1.5 +/- 0.050
B	1.5 +/- 0.050
C	.6 +/- 0.050
D	1.1 +/- 0.050
E	.5 Bsc
F	.2 +/- 0.050
G	.2 +/- 0.050
H	.45 +/- 0.050
J	.12 Ref.

## 1.5 mm DFN-6 Package Dimensions


## Tape and Reel Information:

Guerrilla RF's Tape and Reel specification complies with the Electronics Industries Association (EIA) standards for 'Embossed Carrier Tape of Surface Mount Components for Automatic Handling'. Reference EIA-481. See the table on the following page for Tape and Reel specifications along with units per reel.

Devices are loaded with pins down into the carrier pocket with protective cover tape, wound into a plastic reel. Each reel will be packaged in a cardboard box. There will be product labels on the reel, the protective ESD bag and the outside surface of the box.



**Tape and Reel Packaging with Reel Diameter Noted (D)**



**Carrier Tape Width (W), Pitch (P), Feed Direction and Pin 1 Quadrant Information**



*Released*

# GRF2012

**Broadband Linear Gain Block**  
**0.05 to 6.0 GHz**

Tape and Reel Specification and Device Package Information Table

Package				Carrier Tape			Reel	
Type	Dimensions (mm)	Leads	Weight (mg)	Width (W) (mm)	Pocket Pitch (P) (mm)	Pin 1 Quadrant	Diameter (D) (inches)	Units per Reel
QFN	2.0 x 2.0 x 0.50	12	7	8	4	Q1	7	2500
QFN	3.0 x 3.0 x 0.85	16	24	12	8	Q1	7	1500
DFN	1.5 x 1.5 x 0.45	6	4	8	4	Q1	7	2500
DFN	2.0 x 2.0 x 0.75	8	12	8	4	Q1	7	2500
LFM	3.5 x 3.5 x 0.75	See note	TBD	12	8	Q2	7	1500
LFM	4.0 x 4.0 x 0.75	See note	TBD	12	8	Q2	7	1500

**Note:** Lead count may vary. Reference applicable product data sheet



Released

**GRF2012**

**Broadband Linear Gain Block  
0.05 to 6.0 GHz**

Data Sheet Release Status:	Notes
Advance	S-parameter and NF data based on EM simulations for the fully packaged device using foundry supplied transistor s-parameters. Linearity estimates based on device size, bias condition and experience with related devices.
Preliminary	All data based on evaluation board measurements in the Guerrilla RF Applications Lab.
Released	All data based on device qualification data. Typically, this data is nearly identical to the data found in the preliminary version. Max and min values for key RF parameters are included.

Information in this datasheet is specific to the Guerrilla RF, Inc. ("Guerrilla RF") product identified.

This datasheet, including the information contained in it, is provided by Guerrilla RF as a service to its customers and may be used for informational purposes only by the customer. Guerrilla RF assumes no responsibility for errors or omissions on this datasheet or the information contained herein. Information provided is believed to be accurate and reliable, however, no responsibility is assumed by Guerrilla RF for its use, nor for any infringement of patents, or other rights of third parties, resulting from its use. Guerrilla RF assumes no liability for any datasheet, datasheet information, materials, products, product information, or other information provided hereunder, including the sale, distribution, reproduction or use of Guerrilla RF products, information or materials.

No license, whether express, implied, by estoppel, by implication or otherwise is granted by this datasheet for any intellectual property of Guerrilla RF, or any third party, including without limitation, patents, patent rights, copyrights, trademarks and trade secrets. All rights are reserved by Guerrilla RF.

All information herein, products, product information, datasheets, and datasheet information are subject to change and availability without notice. Guerrilla RF reserves the right to change component circuitry, recommended application circuitry and specifications at any time without prior notice. Guerrilla RF may further change its datasheet, product information, documentation, products, services, specifications or product descriptions at any time, without notice. Guerrilla RF makes no commitment to update any materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

GUERRILLA RF INFORMATION, PRODUCTS, PRODUCT INFORMATION, DATASHEETS AND DATASHEET INFORMATION ARE PROVIDED "AS IS" AND WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. GUERRILLA RF DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. GUERRILLA RF SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Customers are solely responsible for their use of Guerrilla RF products in the Customer's products and applications or in ways which deviate from Guerrilla RF's published specifications, either intentionally or as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Guerrilla RF assumes no liability or responsibility for applications assistance, customer product design, or damage to any equipment resulting from the use of Guerrilla RF products outside of stated published specifications or parameters.

Guerrilla RF Proprietary Information. Guerrilla RF™ and the composite logo of Guerrilla RF™ are trademarks of Guerrilla RF, Inc. ©2014 Guerrilla RF, Inc All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Guerrilla RF:](#)

[GRF2012-EVB](#) [GRF2012](#)