

SnōTM + SnōMākrTM

FPGA Development Kit



Compact, Embeddable Footprint

The speed and performance of FPGA powered acceleration and offload in a small footprint.

Hardware Xcelerator Blocks (XBs)

Take advantage of pre-installed XBs that target application-specific behavior such as floating-point math, motion control and sensor data acquisition.


Programmable with Arduino

Rapidly develop your solution using the free and flexible Arduino IDE.

3 Easy Steps to Higher Performance

①

Buy Snō + SnōMākr Kit



②

Install Arduino IDE



③

Accelerate your IoT Project!



Snō Technical Specifications

- Intel MAX 10 FPGA (16K LE)
- Embedded 8-bit Microcontroller
 - AVR Compatible
 - Selectable 16/32 MHz
- Integrated Hardware Acceleration
 - Pre-installed Xcelerator Blocks
 - Customizable FPGA fabric
- 32 Dedicated Digital, 6 Shared w/ Analog (3.3V)
- 6 Analog Pins
- Program FLASH: 32 KB
- Data Memory SRAM: 2 KB
- ADC Performance
 - Speed: 1 MHz
 - Resolution: 12-bit sustained
 - Sample Rate: 254k samples/second



Kit Includes

- Snō mounted on SnōMākr
- USB Cable

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alorium Technology:](#)

[SNOMAKRKIT](#)