


Recommended PCB Layout



Specifications

Material

Insulator:

Standard: Polyamide, Nylon 6T, UL94V-0

Options: Polymer, LCP, UL94V-0

Polyester, PBT, UL94V-0

Contact: Phosphor Bronze

Plating

See Ordering Grid

Electrical

Current Rating: 3 Amp Per Pin

Contact Resistance: 20 mΩ max.

Insulation Resistance: 1000 MΩ min.

Dielectric Withstand Voltage: 600 V AC

Mechanical & Environmental

Operating Temperature: -40°C to +105°C

Soldering Process

Nylon 6T (Standard)

IR Reflow: 260°C for 10 sec.

Wave: 230°C for 5-10 sec.

Manual Solder: 350°C for 3-5sec

LCP (Option)

IR Reflow: 260°C for 10 sec.

Wave: 250°C for 5-10 sec

Manual Solder: 350°C for 3-5 sec

PBT (Option)

Manual Solder: 330°C for 3-5 sec.


(Not suitable for hi-temp process)

Mates with (Subject to Pin Length)

BG020 BG030 BG031 BG035

BG055 BG060 BG075 BG080

Number of Contacts	Dimensions	
	A	B
2	2.54	5.58
3	5.08	8.12
4	7.62	10.66
5	10.16	13.20
6	12.70	15.74
7	15.24	18.28
8	17.78	20.82
9	20.32	23.36
10	22.86	25.90
11	25.40	28.44
12	27.94	30.98
13	30.48	33.52
14	33.02	36.06
15	35.56	38.60
16	38.10	41.14
17	40.64	43.68
18	43.18	46.22
19	45.72	48.76
20	48.26	51.30
21	50.80	53.84
22	53.34	56.38
23	55.88	58.92
24	58.42	61.46
25	60.96	64.00
26	63.50	66.54
27	66.04	69.08
28	68.58	71.62
29	71.12	74.16
30	73.66	76.70
31	76.20	79.24
32	78.74	81.78
33	81.28	84.32
34	83.82	86.86
35	86.36	89.40
36	88.90	91.94
37	91.44	94.48
38	93.98	97.02
39	96.52	99.56
40	99.06	102.10



Ordering Grid

BG095-XX-X-X-X

No. of Contacts
02 to 40

Contact Plating

A = Gold Flash All Over (Standard)

B = Selective Gold Flash Contact

Area/Tin On Tail

C = Tin All Over

G = 10µ" Gold Contact Area/Tin On Tail

I = 30µ" Gold Contact Area/Tin On Tail

Request Samples
and Quotation

Packing Options

D = Tube (Standard)

E = Tube with Cap

F = Tube with Film

G = Plastic Box

Insulator Material

N = Nylon 6T (Standard)

P = PBT

L = LCP

Part Number		Product Description	
BG095		2.54mm Pitch Socket, Single Row,	
Drawing Date		Through-Hole, Vertical, Dual Beam Folded Contact	
28th December 2007			
By	CC	Tolerances (Except as Noted)	Units:
Detail	BG095 E PCN	Length X. ± 0.30 X.X ± 0.20 X.XX ± 0.15 X.XXX ± 0.10	Metric (mm)
Revision	E3	Angle X.° ± 5° X.X° ± 2° X.XX° ± 1° X.XXX° ± 0.5°	3rd Angle Projection
Date	16/11/17		



This drawing is confidential and
copyright of Global Connector
Technology, Ltd (GCT).
This drawing must not be copied or
disclosed without written
consent. E & OE

GCT
www.gct.co

Not to
Scale

Drawn By
ASS

Sheet No.
1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GCT:](#)

[BG095-14-A-N-D](#)