


DTCxxxxUA-HF Series

RoHS Device
Halogen Free





Features

- Epitaxial planar die construction.
- Built-in biasing resistors, $R_1 \neq R_2$.

Mechanical data

- Case: SOT-323, molded plastic.

Circuit Diagram



Maximum Ratings (at $T_a = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Units
Supply voltage	V_{CC}	50	V
Input voltage	V_{IN}	-5 to +10 -10 to +30 -6 to +40 -5 to +12 -5 to +12 -7 to +20 -5 to +30	V
Output current	I_o	100 100 70 100 100 100 100	mA
Output current	$I_c (\text{Max.})$	100	mA
Power dissipation	P_D	200	mW
Thermal resistance, junction to ambient air	$R_{\theta JA}$	625	$^\circ\text{C/W}$
Operating and storage and temperature range	T_j, T_{STG}	-55 to +150	$^\circ\text{C}$

Electrical Characteristics (at Ta=25°C unless otherwise noted)

Parameter	Symbol	Test conditions	Min	Typ	Max	Units
Input voltage DTC113ZUA-HF DTC114WUA-HF DTC114YUA-HF DTC123JUA-HF DTC123YUA-HF DTC143XUA-HF DTC143ZUA-HF	$V_{I(off)}$	$V_{CC} = 5V, I_o = 100\mu A$	0.3 0.8 0.3 0.5 0.3 0.3 0.5			V
Input voltage DTC113ZUA-HF DTC114WUA-HF DTC114YUA-HF DTC123JUA-HF DTC123YUA-HF DTC143XUA-HF DTC143ZUA-HF	$V_{I(on)}$	$V_o = 0.3V, I_o = 20mA$ $V_o = 0.3V, I_o = 2mA$ $V_o = 0.3V, I_o = 1mA$ $V_o = 0.3V, I_o = 5mA$ $V_o = 0.3V, I_o = 20mA$ $V_o = 0.3V, I_o = 20mA$ $V_o = 0.3V, I_o = 5mA$			3.0 3.0 1.4 1.1 3.0 2.5 1.3	V
Output voltage DTC123JUA-HF DTC143ZUA-HF DTC114YUA-HF All others	$V_{O(on)}$	$I_o / I_i = 5mA / 0.25mA$ $I_o / I_i = 10mA / 0.5mA$		0.1	0.3	V
Input current DTC113ZUA-HF DTC114WUA-HF DTC114YUA-HF DTC123JUA-HF DTC123YUA-HF DTC143XUA-HF DTC143ZUA-HF	I_i	$V_i = 5V$			7.2 0.88 0.88 3.6 3.8 1.8 1.8	mA
Output current	$I_{O(off)}$	$V_{CC} = 50V, V_i = 0V$			0.5	μA
DC current gain DTC113ZUA-HF DTC114WUA-HF DTC114YUA-HF DTC123JUA-HF DTC123YUA-HF DTC143XUA-HF DTC143ZUA-HF	G_I	$V_o = 5V, I_o = 10mA$	33 24 68 80 33 30 80			
Input resistor DTC113ZUA-HF DTC114WUA-HF DTC114YUA-HF DTC123JUA-HF DTC123YUA-HF DTC143XUA-HF DTC143ZUA-HF	$R_1(R_2)$			1(10) 10(4.7) 10(47) 2.2(47) 2.2(10) 4.7(10) 4.7(47)		k Ω
Input resistor (R_1) tolerance	ΔR_1		-30		+30	%
Resistance ratio tolerance	$\Delta R_2/R_1$		-20		+20	%
Gain-bandwidth product	f_r	$V_{CE} = 10V, I_E = 5mA, f = 100MHz$		250		MHz

Rating and Characteristic Curves (DTCxxxxUA-HF Series)

Fig.1 - Derating Curve




Fig.2 - $V_{CE(SAT)}$ vs. I_C




Fig.3 - DC Current Gain




Fig.4 - Output Capacitance




Fig.5 - Collector Current vs. Input Voltage








Fig.6 - Input Voltage vs. Collector Current



Company reserves the right to improve product design, functions and reliability without notice.

REV:A

Reel Taping Specification



	SYMBOL	A	B	C	d	D	D1	D2
SOT-323	(mm)	2.25 ± 0.10	2.55 ± 0.10	1.20 ± 0.10	1.50 ± 0.10	178.00 ± 1.00	54.00 ± 0.50	13.00 ± 0.50
	(inch)	0.089 ± 0.004	0.100 ± 0.004	0.047 ± 0.004	0.059 ± 0.004	7.008 ± 0.039	2.126 ± 0.020	0.512 ± 0.020


	SYMBOL	E	F	P	P0	P1	W	W1
SOT-323	(mm)	1.75 ± 0.10	3.50 ± 0.05	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.05	8.00 + 0.30 - 0.10	9.50 ± 1.00
	(inch)	0.069 ± 0.004	0.138 ± 0.002	0.157 ± 0.004	0.157 ± 0.004	0.079 ± 0.002	0.315 + 0.012 - 0.004	0.374 ± 0.039

Company reserves the right to improve product design , functions and reliability without notice.

REV:A

Marking Code

Part Number	Marking Code
DTC113ZUA-HF	E21
DTC114WUA-HF	84
DTC114YUA-HF	64
DTC123JUA-HF	E42
DTC123YUA-HF	62
DTC143XUA-HF	43•
DTC143ZUA-HF	E23




xx/xxx = Product type marking code

Suggested PAD Layout

SIZE	SOT-323	
	(mm)	(inch)
A	0.90	0.035
B	0.70	0.028
C	1.30	0.051
D	1.90	0.075

Note: 1.The pad layout is for reference purposes only.



Standard Packaging

Case Type	REEL PACK	
	REEL (pcs)	Reel Size (inch)
SOT-323	3,000	7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Comchip Technology:](#)

[DTC113ZUA-HF](#) [DTC143XUA-HF](#) [DTC114YUA-HF](#) [DTC123YUA-HF](#) [DTC114WUA-HF](#) [DTC123JUA-HF](#)
[DTC143ZUA-HF](#)