


AES2AF-HF Thru. AES2KF-HF

Reverse Voltage: 50 to 800 Volts

Forward Current: 2.0 Amp

RoHS Device

Halogen Free




Features

- For surface mounted applications.
- Low profile package.
- Low forward voltage drop.
- High surge current capability.
- AEC-Q101 Qualified.

Mechanical data

- Case: SMAF, molded plastic.
- Epoxy: UL flammability classification rating 94V-0.
- Terminals: Solder plated, solderable per MIL-STD-202, method 208.
- Polarity: Color band denoted cathode end.



Circuit Diagram



Maximum Ratings (at TA=25°C unless otherwise specified)

Parameter	Symbols	AES2AF -HF	AES2BF -HF	AES2CF -HF	AES2DF -HF	AES2EF -HF	AES2GF -HF	AES2HF -HF	AES2JF -HF	AES2KF -HF	Units
Peak repetitive reverse voltage	V _{RRM}	50	100	150	200	300	400	500	600	800	V
RMS reverse voltage	V _{RMS}	35	70	105	140	210	280	350	420	560	V
DC blocking voltage	V _{DC}	50	100	150	200	300	400	500	600	800	V
Max. average forward output current	I _{F(AV)}	2									A
Peak forward surge current, 8.3ms single half sine-wave	I _{FSM}	50									A
Typical thermal resistance (Note 1)	R _{θJA}	78									°C/W
	R _{θJC}	18									
	R _{θJL}	20									
Operating junction temperature range	T _J	-55 ~ +150									°C
Storage temperature range	T _{STG}	-55 ~ +150									°C

Notes: 1. Device mounted on PCB with 10mm x 20mm x 0.1mm copper pad areas.

Electrical Characteristics (at $T_A=25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbols	Test Conditions			Typ	Max	Units
Max. instantaneous forward voltage	V_F	$I_F=2.0\text{A}$	@ $T_A=25^\circ\text{C}$	AES2AF-HF AES2BF-HF AES2CF-HF AES2DF-HF		0.95	V
				AES2EF-HF AES2GF-HF		1.25	
				AES2HF-HF AES2JF-HF		1.7	
				AES2KF-HF		2.3	
Max. reverse current	I_R	Rated V_R	@ $T_A=25^\circ\text{C}$	AES2AF-HF~AES2JF-HF		5	μA
			@ $T_A=125^\circ\text{C}$	AES2KF-HF		10	
						200	
Max. reverse recovery time	t_{rr}	$I_F=0.5\text{A}$, $I_{RM}=1\text{A}$, $I_{R(REC)}=0.25\text{A}$				35	ns

Rating and Characteristic Curves (AES2AF-HF Thru. AES2DF-HF)

Fig.1 - Forward Current Derating Curve




Fig.2 - Surge Current Derating Curve




Fig.3 - Typical Forward Voltage Characteristic





Fig.4 - Typical Reverse Characteristic



Rating and Characteristic Curves (AES2EF-HF Thru. AES2GF-HF)

Fig.5 - Forward Current Derating Curve




Fig.6 - Surge Current Derating Curve




Fig.7 - Typical Forward Voltage Characteristic





Fig.8 - Typical Reverse Characteristic



Rating and Characteristic Curves (AES2HF-HF Thru. AES2JF-HF)

Fig.9 - Forward Current Derating Curve




Fig.10 - Surge Current Derating Curve




Fig.11 - Typical Forward Voltage Characteristic





Fig.12 - Typical Reverse Characteristic



Rating and Characteristic Curves (AES2KF-HF)

Fig.13 - Forward Current Derating Curve




Fig.14 - Surge Current Derating Curve




Fig.15 - Typical Forward Voltage Characteristic






Fig.16 - Typical Reverse Characteristic



Reel Taping Specification




SMAF	SYMBOL	A	B	C	d	D	D1	D2
	(mm)	2.93 ± 0.10	5.45 ± 0.10	1.10 ± 0.10	1.55 ± 0.10	330 ± 1.00	75.00 ± 1.00	13.50 ± 0.50
	(inch)	0.115 ± 0.004	0.215 ± 0.004	0.043 ± 0.004	0.061 ± 0.004	12.992 ± 0.039	2.953 ± 0.039	0.531 ± 0.020

SMAF	SYMBOL	E	F	P	P0	P1	T	W	W1
	(mm)	1.75 ± 0.10	5.50 ± 0.05	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.10	0.23 ± 0.05	12.00 ± 0.10	13.50 ± 1.00
	(inch)	0.069 ± 0.004	0.217 ± 0.002	0.157 ± 0.004	0.157 ± 0.004	0.079 ± 0.004	0.009 ± 0.002	0.472 ± 0.004	0.531 ± 0.039

Company reserves the right to improve product design , functions and reliability without notice.


Marking Code

Part Number	Marking Code
AES2AF-HF	ES2AF
AES2BF-HF	ES2BF
AES2CF-HF	ES2CF
AES2DF-HF	ES2DF
AES2EF-HF	ES2EF
AES2GF-HF	ES2GF
AES2HF-HF	ES2HF
AES2JF-HF	ES2JF
AES2KF-HF	ES2KF



Suggested PAD Layout

SIZE	SMAF	
	(mm)	(inch)
A	4.18	0.165
B	2.08	0.082
C	1.67	0.066



Note: 1. The pad layout is for reference purpose only.

Standard Packaging

Case Type	REEL PACK	
	REEL (pcs)	Reel Size (inch)
SMAF	10,000	13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Comchip Technology:](#)

[AES2HF-HF](#) [AES2JF-HF](#) [AES2KF-HF](#) [AES2EF-HF](#) [AES2AF-HF](#) [AES2CF-HF](#) [AES2GF-HF](#) [AES2DF-HF](#)
[AES2BF-HF](#)