




R1 Type





R2 Type



Recommended PCB Layouts

Solder Area



Specifications

Material

Insulator: Polymer, LCP, UL94V-0
Polyamide, Nylon 6T, UL94V-0
Contact: Copper Alloy

Plating

See Ordering Grid

Electrical

Current Rating: 1A per pin
Contact Resistance: 20 mΩ max.
Insulating Resistance: 1000 MΩ min.
Dielectric Withstand Voltage: 300V AC

Mechanical & Environmental

Operating Temperature: -40°C to +105°C


Maximum Table		
Insulator Height 'H'	OL Max (mm)	Dim C Max (mm)
A	12.00	8.00
K	10.00	6.00
B	15.00	10.00

Soldering Process: (LCP & Nylon 6T)
IR Reflow: 260°C for 10 sec.
Manual Solder: 350°C for 3-5 sec

Mates with (Subject to pin length)

BD074 BD075 BD080 BD090

BD074 Recommended mating length 1.50mm



No. of Contacts	Dimensions	
	A	B
2	2.54	1.27
3	3.81	2.54
4	5.08	3.81
5	6.35	5.08
6	7.62	6.35
7	8.89	7.62
8	10.16	8.89
9	11.43	10.16
10	12.70	11.43
11	13.97	12.70
12	15.24	13.97
13	16.51	15.24
14	17.78	16.51
15	19.05	17.78
16	20.32	19.05
17	21.59	20.32

No. of Contacts	Dimensions	
	A	B
18	22.86	21.59
19	24.13	22.86
20	25.40	24.13
21	26.67	25.40
22	27.94	26.67
23	29.21	27.94
24	30.48	29.21
25	31.75	30.48
26	33.02	31.75
27	34.29	33.02
28	35.56	34.29
29	36.83	35.56
30	38.10	36.83
31	39.37	38.10
32	40.64	39.37
33	41.91	40.64

Ordering Grid

BD021-XXX-XX-XXXX-XXXX-XXXX-XX
No. of Contacts: 02 to 33

Contact Plating

A = Gold Flash All Over (Standard)
B = Selective Gold Flash Contact Area/
Tin On Tail
C = Tin All Over
G = 10μ" Gold Contact Area/Tin On Tail
I = 30μ" Gold Contact Area/Tin On Tail

Insulator Height 'H'

A = 1.50mm (Standard)
K = 1.00mm
B = 2.00mm

Type
1 = R1 Type
2 = R2 Type

Dimension C (Post Height) (1/100mm)

0150 = 1.50mm (Standard)
0350 = 3.50mm (Standard)
or specify custom Post Height
eg 2.50mm = 0250
(Minimum 0100 = 1.00mm)
(Maximum - see Table)

Request Samples and Quotation

Packing Options

B = Tape & Reel w/Cap (Standard)
D = Tube
E = Tube with Cap

Insulator Material

L = LCP
N = Nylon 6T

Dimension E (Footprint Width) (1/100mm)

0550 = 5.50mm (Standard)
or specify custom Footprint width
eg 0500 = 5.00mm
(Tooling charge may apply)

Dimension D (PCB to Top of Insulator) (1/100mm)

0150 = 1.50mm (Standard - Minimum where 'H' = K)
0200 = 2.00mm (Standard - Minimum where 'H' = A)
0240 = 2.40mm (Standard - Minimum where 'H' = B)
or specify custom PCB to top of Insulator Height
eg 0250 = 2.50mm

Part Number		Product Description	
BD021		1.27mm Pitch Pin Header	
Drawing Date		Single Row, Surface Mount, Vertical	
27th March 2008			
By	CC	Tolerances (Except as Noted)	Units:
Detail	BD021	Length	Metric (mm)
Revision	D4	Angle	
Date	07/09/17	X.X ± 0.38	X.X° ± 5°
		X.XX ± 0.25	X.XX° ± 2°
		X.XXX ± 0.13	X.XXX° ± 1°
			X.XXX° ± 0.5°

This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE

GCT
www.gct.co

Not to Scale	Drawn By ASE	Sheet No. 1/1
--------------	--------------	---------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GCT:](#)

[BD021-04A-A1-0350-0200-0550-LD](#) [BD021-05A-A1-0350-0200-0550-LD](#) [BD021-06A-A1-0350-0200-0550-LD](#)
[BD021-07A-A1-0350-0200-0550-LD](#) [BD021-08A-A1-0350-0200-0550-LD](#) [BD021-09A-A1-0350-0200-0550-LD](#) [BD021-](#)
[10A-A1-0350-0200-0550-LD](#) [BD021-11A-A1-0350-0200-0550-LD](#) [BD021-12A-A1-0350-0200-0550-LD](#) [BD021-13A-A1-](#)
[0350-0200-0550-LD](#) [BD021-14A-A1-0350-0200-0550-LD](#) [BD021-15A-A1-0350-0200-0550-LD](#) [BD021-16A-A1-0350-](#)
[0200-0550-LD](#) [BD021-17A-A1-0350-0200-0550-LD](#) [BD021-18A-A1-0350-0200-0550-LD](#) [BD021-19A-A1-0350-0200-](#)
[0550-LD](#) [BD021-20A-A1-0350-0200-0550-LD](#) [BD021-21A-A1-0350-0200-0550-LD](#) [BD021-22A-A1-0350-0200-0550-LD](#)
[BD021-23A-A1-0350-0200-0550-LD](#) [BD021-24A-A1-0350-0200-0550-LD](#) [BD021-25A-A1-0350-0200-0550-LD](#)
[BD021-26A-A1-0350-0200-0550-LD](#) [BD021-27A-A1-0350-0200-0550-LD](#) [BD021-28A-A1-0350-0200-0550-LD](#) [BD021-](#)
[29A-A1-0350-0200-0550-LD](#) [BD021-30A-A1-0350-0200-0550-LD](#) [BD021-31A-A1-0350-0200-0550-LD](#) [BD021-32A-A1-](#)
[0350-0200-0550-LD](#) [BD021-33A-A1-0350-0200-0550-LD](#)