



Recommended PCB Layout



Contacts	Dimensions	
	A	B
4	2.0	4.20
6	4.0	6.20
8	6.0	8.20
10	8.0	10.20
12	10.0	12.20
14	12.0	14.20
16	14.0	16.20
18	16.0	18.20
20	18.0	20.20
22	20.0	22.20
24	22.0	24.20
26	24.0	26.20
28	26.0	28.20
30	28.0	30.20
32	30.0	32.20
34	32.0	34.20
36	34.0	36.20
38	36.0	38.20
40	38.0	40.20
42	40.0	42.20
44	42.0	44.20
46	44.0	46.20
48	46.0	48.20
50	48.0	50.20

Operating Temperature: -40°C to +105°C

BF110 BF112

(Minimum 0550 = 5.50mm)

equivalent to $\dim D$ minus 3.00mm)

Part Number		Product Description	
BF135		2.00mm Pitch Pin Header, Dual Row, Surface Mount, Horizontal	
Drawing Date			
31st October 2007			
By	CC	Tolerances (Except as Noted)	Units:
		Length	Metric (mm)
Detail	BF135 F PCN	$X, \pm 0.30$ $X, X \pm 0.20$	$X, \pm 5^\circ$ $X, \pm 2^\circ$
Revision	F5	$X, X, X \pm 0.15$	$X, X, X \pm 1^\circ$
Date	28/04/23	$X, XXX, \pm 0.10$	$X, XXX, \pm 0.5^\circ$
		 Third Angle Projection	
			
		 This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE	



Not to Scale	Drawn By LYH	Sheet No. 1/1
-----------------	-----------------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GCT:](#)

[BF135-14-A-0400-0700-0400-L-B](#) [BF135-04-A-0200-0700-0400-L-C](#) [BF135-04-A-0400-0700-0400-L-C](#) [BF135-06-A-0200-0700-0400-L-C](#) [BF135-06-A-0400-0700-0400-L-C](#) [BF135-08-A-0200-0700-0400-L-C](#) [BF135-08-A-0400-0700-0400-L-C](#) [BF135-10-A-0200-0700-0400-L-C](#) [BF135-10-A-0400-0700-0400-L-C](#) [BF135-12-A-0200-0700-0400-L-C](#) [BF135-12-A-0400-0700-0400-L-C](#) [BF135-14-A-0200-0700-0400-L-C](#) [BF135-14-A-0400-0700-0400-L-C](#) [BF135-16-A-0200-0700-0400-L-C](#) [BF135-16-A-0400-0700-0400-L-C](#) [BF135-18-A-0200-0700-0400-L-C](#) [BF135-18-A-0400-0700-0400-L-C](#) [BF135-20-A-0200-0700-0400-L-C](#) [BF135-20-A-0400-0700-0400-L-C](#)