


## AMMBT2222A-HF (NPN)

RoHS Device  
Halogen Free



### Features



- Epoxy meets UL-94 V-0 flammability rating.
- Moisture sensitivity Level 1.
- High conductance.
- AEC-Q101 Qualified

### Mechanical data

- Case: SOT-23, molded plastic.
- Terminals: Tin plated leads, solderable per J-STD-002 and JESD22-B102.

### Circuit diagram

1. Base  
2. Emitter  
3. Collector



### Maximum Ratings (at Ta=25°C unless otherwise noted)

| Parameter                    | Symbol    | Value       | Unit |
|------------------------------|-----------|-------------|------|
| Collector-base voltage       | $V_{CBO}$ | 75          | V    |
| Collector-emitter voltage    | $V_{CEO}$ | 40          | V    |
| Emitter-base voltage         | $V_{EBO}$ | 6           | V    |
| Collector current-continuous | $I_C$     | 600         | mA   |
| Total device dissipation     | $P_D$     | 300         | mW   |
| Junction temperature range   | $T_J$     | -55 to +150 | °C   |
| Storage temperature range    | $T_{STG}$ | -55 to +150 | °C   |

## Electrical Characteristics (at Ta=25°C unless otherwise noted)

| Parameter                            | Conditions                                                           | Symbol        | Min | Max        | Unit |
|--------------------------------------|----------------------------------------------------------------------|---------------|-----|------------|------|
| Collector-base breakdown voltage     | $I_C = 10\mu A, I_E = 0$                                             | $V_{(BR)CBO}$ | 75  |            | V    |
| Collector-emitter breakdown voltage  | $I_C = 10mA, I_B = 0$                                                | $V_{(BR)CEO}$ | 40  |            | V    |
| Emitter-base breakdown voltage       | $I_E = 10\mu A, I_C = 0$                                             | $V_{(BR)EBO}$ | 6   |            | V    |
| Collector cut-off current            | $V_{CE} = 60V, V_{BE} = 3V$                                          | $I_{CEX}$     |     | 10         | nA   |
| Base cut-off current                 | $V_{CE} = 60V, I_C = 0$                                              | $I_{CBO}$     |     | 100        | nA   |
| Emitter cut-off current              | $V_{EB} = 3V, I_C = 0$                                               | $I_{EBO}$     |     | 100        | nA   |
| DC current gain                      | $V_{CE} = 10V, I_C = 0.1mA$                                          | $h_{FE(1)}$   | 35  |            |      |
|                                      | $V_{CE} = 10V, I_C = 1mA$                                            | $h_{FE(2)}$   | 50  |            |      |
|                                      | $V_{CE} = 10V, I_C = 10mA$                                           | $h_{FE(3)}$   | 75  |            |      |
|                                      | $V_{CE} = 10V, I_C = 150mA$                                          | $h_{FE(4)}$   | 100 | 300        |      |
|                                      | $V_{CE} = 10V, I_C = 500mA$                                          | $h_{FE(5)}$   | 40  |            |      |
|                                      | $V_{CE} = 1V, I_C = 150mA$                                           | $h_{FE(6)}$   | 50  |            |      |
| Collector-emitter saturation voltage | $I_C = 150mA, I_B = 15mA$<br>$I_C = 500mA, I_B = 50mA$               | $V_{CE(sat)}$ |     | 0.3<br>1.0 | V    |
| Base-emitter saturation voltage      | $I_C = 150mA, I_B = 15mA$<br>$I_C = 500mA, I_B = 50mA$               | $V_{BE(sat)}$ | 0.6 | 1.2<br>2.0 | V    |
| Transition frequency                 | $V_{CE} = 20V, I_C = 20mA, f = 100MHz$                               | $f_T$         | 300 |            | MHz  |
| Delay time                           | $V_{CC} = 30V, V_{BE(off)} = -0.5V,$<br>$I_C = 150mA, I_{B1} = 15mA$ | $t_d$         |     | 10         | ns   |
| Rise time                            |                                                                      | $t_r$         |     | 25         | ns   |
| Storage time                         | $V_{CC} = 30V, I_C = 150mA, I_{B1} = I_{B2} = 15mA$                  | $t_s$         |     | 225        | ns   |
| Fall time                            |                                                                      | $t_f$         |     | 60         | ns   |

Rating and Characteristic Curves (AMMBT2222A-HF)

Fig.1 - Static Characteristic




Fig.2 -  $H_{FE}$  —  $I_C$




Fig.3 -  $V_{BEsat}$  —  $I_C$






Fig.4 -  $V_{CEsat}$  —  $I_C$



Reel Taping Specification




| SOT-23 | SYMBOL | A             | B             | C             | d                        | D             | D1            | D2            |
|--------|--------|---------------|---------------|---------------|--------------------------|---------------|---------------|---------------|
|        | (mm)   | 3.15 ± 0.10   | 2.77 ± 0.10   | 1.22 ± 0.10   | 1.50 + 0.10<br>- 0.00    | 178.00 ± 1.00 | 54.60 ± 1.00  | 13.30 ± 1.00  |
|        | (inch) | 0.124 ± 0.004 | 0.109 ± 0.004 | 0.048 ± 0.004 | 0.059 + 0.004<br>- 0.000 | 7.008 ± 0.039 | 2.150 ± 0.039 | 0.524 ± 0.039 |

| SOT-23 | SYMBOL | E             | F             | P             | P0            | P1            | W                        | W1            |
|--------|--------|---------------|---------------|---------------|---------------|---------------|--------------------------|---------------|
|        | (mm)   | 1.75 ± 0.10   | 3.50 ± 0.05   | 4.00 ± 0.10   | 4.00 ± 0.10   | 2.00 ± 0.05   | 8.00 + 0.30<br>- 0.10    | 11.10 ± 0.20  |
|        | (inch) | 0.069 ± 0.004 | 0.138 ± 0.002 | 0.157 ± 0.004 | 0.157 ± 0.004 | 0.079 ± 0.002 | 0.315 + 0.012<br>- 0.004 | 0.437 ± 0.008 |

Marking Code


| Part Number   | Marking Code |
|---------------|--------------|
| AMMBT2222A-HF | 1P.          |



Suggested PAD Layout

| SIZE | SOT-23 |        |
|------|--------|--------|
|      | (mm)   | (inch) |
| A    | 0.90   | 0.035  |
| B    | 0.80   | 0.031  |
| C    | 0.95   | 0.037  |
| D    | 2.00   | 0.079  |
| E    | 2.90   | 0.114  |

Note: 1. The pad layout is for reference purposes only.



Standard Packaging

| Case Type | REEL PACK  |                  |
|-----------|------------|------------------|
|           | REEL (pcs) | Reel Size (inch) |
| SOT-23    | 3,000      | 7                |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Comchip Technology:](#)

[AMMBT2222A-HF](#)