




Recommended PCB Layout



2° Max. Sway & Toe
(Either Direction At The top)



Specifications

Material

Insulator:

Standard: Polyamide, Nylon 6T, UL94V-0

Options: Polymer, LCP, UL94V-0

Polyester, PBT, UL94V-0

Contact: Copper Alloy

Plating

Contact: See ordering grid

Electrical

Current Rating: 3 Amp Per Pin

Contact Resistance: 20 mΩ max.

Insulation Resistance : 1000 MΩ min.

Dielectric Withstand Voltage: 600 V AC

Mechanical & Environmental

Operating Temperature: -40°C to +105°C

Soldering Process

Nylon 6T (Standard)

IR Reflow: 260°C for 10 sec.

Wave: 230°C for 5-10 sec

Manual Solder : 350°C for 3-5 sec

LCP (Option)

IR Reflow: 260°C for 10 sec.

Wave: 250°C for 5-10 sec.

Manual Solder: 350°C for 3-5sec

PBT (Option)

Manual Solder: 330°C for 3-5sec

(not suitable for hi-temp process)

Mates with (Subject to Pin Length)

BG090 BG095 BG096 BG100 BG110

BG115 BG125 BG126 BG130 BG135

BG145 BG205 BG230

BG090 Recommended mating length 4.00mm

BG095 Recommended mating length 4.00mm

Number of Contacts	Dimensions	
	A	B
1	/	2.54
2	2.54	5.08
3	5.08	7.62
4	7.62	10.16
5	10.16	12.70
6	12.70	15.24
7	15.24	17.78
8	17.78	20.32
9	20.32	22.86
10	22.86	25.40
11	25.40	27.94
12	27.94	30.48
13	30.48	33.02
14	33.02	35.56
15	35.56	38.10
16	38.10	40.64
17	40.64	43.18
18	43.18	45.72
19	45.72	48.26
20	48.26	50.80
21	50.80	53.34
22	53.34	55.88
23	55.88	58.42
24	58.42	60.96
25	60.96	63.50
26	63.50	66.04
27	66.04	68.58
28	68.58	71.12
29	71.12	73.66
30	73.66	76.20
31	76.20	78.74
32	78.74	81.28
33	81.28	83.82
34	83.82	86.36
35	86.36	88.90
36	88.90	91.44
37	91.44	93.98
38	93.98	96.52
39	96.52	99.06
40	99.06	101.60

Ordering Grid

BG030-XX-X-XXXX-XXXX-X-X Request Samples and Quotation

No. of Contacts
01 to 40

Contact Plating

A = Gold Flash All Over (Standard)

B = Selective Gold Flash Contact

Area/Tin On Tail

C = Tin All Over

G = 10μ" Gold Contact Area/Tin On Tail

I = 30μ" Gold Contact Area/Tin On Tail

L = Matte Tin

Dimension C (1/100mm) (Post Height)

0400 = 4.00mm (Standard)

0450 = 4.50mm (Standard)

0650 = 6.50mm (Standard)

Or specify custom Post Height

e.g. 0250 = 2.50mm

(Maximum 2000=20.00mm)

(Minimum 0050=0.50mm)

Packing Options

G = Plastic Box (Standard)

B = Tape & Reel with Cap

D = Tube

E = Tube with Cap

Insulator Material

N = Nylon 6T (Standard)

P = PBT

L = LCP

Dimension D (1/100mm) (Tail Length)

0300 = 3.00mm (Standard)

Or specify custom Tail Length

e.g. 0250 = 2.50mm

(Maximum 2000=20.00mm)

(Minimum 0050=0.50mm)

Part Number	Product Description		
BG030	2.54mm pitch Pin Header		
Drawing Date	Single Row, Through-Hole, Vertical		
1st November 2006			
By	CC	Tolerances (Except as Noted)	Units:
Detail	BG030 G PCN	Length X. ± 0.30 X.X ± 0.20 X.XX ± 0.15 X.XXX ± 0.10	Metric (mm)
Revision	G5	Angle X." ± 5° X.X" ± 2° X.XX" ± 1° X.XXX" ± 0.5°	3rd Angle Projection
Date	06/09/17		



This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE

GCT
www.gct.co

Not to Scale
Drawn By LYH
Sheet No. 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GCT:](#)

[BG030-03-A-0650-0300-N-G](#) [BG030-04-A-0650-0300-N-G](#) [BG030-06-A-0650-0300-N-G](#) [BG030-07-A-0650-0300-N-G](#) [BG030-08-A-0450-0300-N-G](#) [BG030-08-A-0650-0300-N-G](#) [BG030-09-A-0450-0300-N-G](#) [BG030-09-A-0650-0300-N-G](#) [BG030-10-A-0450-0300-N-G](#) [BG030-10-A-0650-0300-N-G](#) [BG030-11-A-0450-0300-N-G](#) [BG030-11-A-0650-0300-N-G](#) [BG030-12-A-0450-0300-N-G](#) [BG030-12-A-0650-0300-N-G](#) [BG030-13-A-0450-0300-N-G](#) [BG030-13-A-0650-0300-N-G](#) [BG030-14-A-0450-0300-N-G](#) [BG030-14-A-0650-0300-N-G](#) [BG030-15-A-0450-0300-N-G](#) [BG030-15-A-0650-0300-N-G](#) [BG030-16-A-0450-0300-N-G](#) [BG030-16-A-0650-0300-N-G](#) [BG030-17-A-0450-0300-N-G](#) [BG030-17-A-0650-0300-N-G](#) [BG030-18-A-0450-0300-N-G](#) [BG030-18-A-0650-0300-N-G](#) [BG030-19-A-0450-0300-N-G](#) [BG030-19-A-0650-0300-N-G](#) [BG030-20-A-0450-0300-N-G](#) [BG030-20-A-0650-0300-N-G](#) [BG030-21-A-0450-0300-N-G](#) [BG030-21-A-0650-0300-N-G](#) [BG030-22-A-0450-0300-N-G](#) [BG030-22-A-0650-0300-N-G](#) [BG030-23-A-0450-0300-N-G](#) [BG030-23-A-0650-0300-N-G](#) [BG030-24-A-0450-0300-N-G](#) [BG030-24-A-0650-0300-N-G](#) [BG030-25-A-0450-0300-N-G](#) [BG030-25-A-0650-0300-N-G](#) [BG030-26-A-0450-0300-N-G](#) [BG030-26-A-0650-0300-N-G](#) [BG030-27-A-0450-0300-N-G](#) [BG030-27-A-0650-0300-N-G](#) [BG030-28-A-0450-0300-N-G](#) [BG030-28-A-0650-0300-N-G](#) [BG030-29-A-0450-0300-N-G](#) [BG030-29-A-0650-0300-N-G](#) [BG030-30-A-0450-0300-N-G](#) [BG030-30-A-0650-0300-N-G](#) [BG030-31-A-0450-0300-N-G](#) [BG030-31-A-0650-0300-N-G](#) [BG030-32-A-0450-0300-N-G](#) [BG030-32-A-0650-0300-N-G](#) [BG030-33-A-0450-0300-N-G](#) [BG030-33-A-0650-0300-N-G](#) [BG030-34-A-0450-0300-N-G](#) [BG030-34-A-0650-0300-N-G](#) [BG030-35-A-0450-0300-N-G](#) [BG030-35-A-0650-0300-N-G](#) [BG030-36-A-0450-0300-N-G](#) [BG030-36-A-0650-0300-N-G](#) [BG030-37-A-0450-0300-N-G](#) [BG030-37-A-0650-0300-N-G](#) [BG030-38-A-0450-0300-N-G](#) [BG030-38-A-0650-0300-N-G](#) [BG030-39-A-0450-0300-N-G](#) [BG030-39-A-0650-0300-N-G](#) [BG030-40-A-0450-0300-N-G](#) [BG030-40-A-0650-0300-N-G](#)