

Low Loss Power Distribution Switch With Programmable Current limit

General Description

The SY28892Z protection switch is an ultra-low on resistance, compact device with resistor programmable current limit. The device provides an open-drain fault flag output to signal over-current and fault conditions. It incorporates short circuit protection, over-temperature protection, and a reverse current blocking function.

The SY28892Z is available in a compact 2 mm×2mm DFN-6 package.


Features

- Input Voltage: 2.5V to 5.5V
- Low Power Path Resistance: 65mΩ (Typ.)
- Adjustable Current Limit up to 2.0A
- Over-Temperature Shutdown and Automatic Retry
- Reverse Blocking (No Body Diode)
- Open-Drain Fault Flag (OCB) Output for Over-Current and Fault Conditions
- Built-in Soft-Start
- Compact Package: DFN2×2-6

Applications

- USB 3.1 Applications
- USB 3G Data Cards
- USB Dongles
- Mini PCI Accessories
- USB Chargers
- Public Multi-USB Chargers
- PC Card Hot Swap Applications

Typical Application Circuit



Note: If 1μF input cap will lead to large Vin voltage spike, it is strongly recommended to add additional 10μF ceramic cap.


Figure 1. Schematic Diagram

Ordering Information

Ordering Part Number	Package Type	Top Mark
SY28892ZDEC	DFN2x2-6 RoHS Compliant and Halogen Free	nBxyz

x=year code, y=week code, z= lot number code

Pinout (top view)



Pin Name	Pin Number	Pin Description
OUT	1	Output pin, decoupled with a 10μF capacitor to GND.
ISET	2	Current limit programming pin. Connect a resistor R_{SET} from this pin to the ground to program the current limit: $I_{LIM} (A) = 230/R_{SET} (\Omega)$.
OCB	3	Open-drain fault flag.
EN	4	ON/OFF control, active high. Do not leave it floating.
GND	5, Exposed Pad	Ground pin.
IN	6	Input pin, decoupled with a ceramic capacitor to GND.

Block Diagram




Figure 2. Block Diagram

Absolute Maximum Ratings

Parameter (Note 1)	Min	Max	Unit
IN, OUT, ISET, OCB, EN	-0.3	7	V
Lead Temperature (Soldering, 10s)		260	
Junction Temperature, Operating	-40	150	°C
Storage Temperature	-65	150	

Thermal Information

Parameter (Note 2)	Typ	Unit
θ_{JA} Junction-to-Ambient Thermal Resistance	65.3	°C/W
θ_{JC} Junction-to-Case Thermal Resistance	16.2	
P_D Power Dissipation $T_A = 25^\circ\text{C}$	1.53	W

Recommended Operating Conditions

Parameter (Note 3)	Min	Max	Unit
IN, OUT	2.5	5.5	V
ISET, OCB, EN	0	5.5	
Junction Temperature, Operating	-40	125	°C
Ambient Temperature	-40	105	

Electrical Characteristics

($V_{IN} = 5V$, $C_{OUT} = 10\mu F$, $T_A = 25^\circ\text{C}$, BOLD values indicate -40°C to 125°C , unless otherwise specified. The values are guaranteed by test, design, or statistical correlation.)

Parameter		Symbol	Test Conditions	Min	Typ	Max	Unit
Input Voltage Range		V _{IN}		2.5		5.5	V
IN UVLO Threshold		V _{IN,UVLO}		2.0		2.45	V
IN UVLO Hysteresis		V _{IN,HYS}			0.1		V
Shutdown Input Current		I _{SHDN}	Open load, switch off		0.1	6	μA
			Output grounded, switch off		0.1	40	μA
Reverse Leakage Current			IN tied to GND, V _{OUT} =5V		0.1	40	μA
Reverse Blocking Threshold		V _{RBT}	V _{OUT} -V _{IN}		100		mV
Reverse Blocking Recovery Threshold		V _{RBT_REC}	V _{OUT} -V _{IN}		-30		mV
Quiescent Supply Current		I _Q	No load, switch on		45	100	μA
FET R _{DS(ON)}		R _{DS(ON)}	V _{IN} =5V, I _{OUT} =0.5A		65	100	mΩ
Current Limit		I _{LIM}	V _{OUT} =4V, R _{SET} =460Ω (Note5)	0.425	0.5	0.575	A
			V _{OUT} =4V, R _{SET} =153.3Ω(Note5)	1.382	1.5	1.617	A
EN/ \overline{EN} Threshold	Logic-low Voltage	V _{IL}				0.4	V
	Logic-high Voltage	V _{IH}		1.2			V
EN Input Capacitance		C _{EN}	(Note4)		1		pF

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
EN Leakage Current	I _{ENLK}				1	μA
Output Turn-On Time	t _{ON}	R _L =10Ω, C _L =1μF. Measure from EN ON to V _{OUT} reach V _{IN} ×90%	0.9	2	5	ms
Output Turn-On Rise Time	t _R	R _L =10Ω, C _L =1μF. Measure from V _{OUT} =10% of V _{IN} to 90% of V _{IN}	0.9	2	5	ms
Output Turn-Off Time	t _{OFF}	R _L =10Ω, C _L =1μF. Measure from EN OFF to V _{OUT} reach V _{IN} ×10%		22		μs
Output Turn-Off Fall Time	t _F	R _L =10Ω, C _L =1μF. Measure from V _{OUT} =90% of V _{IN} to 10% of V _{IN}		21		μs
OCB Low Resistance	R _{OCB}	V _{IN} =5V, I _L =10μA		9		Ω
		V _{IN} =3.3V, I _L =10μA		12		Ω
OUT Shutdown Discharge Resistance	R _{DSG}	EN=0, V _{OUT} =0.1V		25		Ω
OCB Leakage Current	I _{LKG_OCB}	V _{OCB} =5V		0.01	1	μA
Thermal Shutdown Temperature	T _{SD}			150		°C
Thermal Shutdown Hysteresis	T _{HYS}			20		°C
Current Limit Response Time	t _{OC_RES}	I _{LOAD} =1.2I _{LIMIT} (Note 5)		25		μs
Short Circuit Response Time	t _{OC}	I _{LOAD} =1.5I _{LIMIT} (Note 5)		2		μs
Over Current Flag Response Time	t _{OCB}	I _{LOAD} =1.2I _{LIMIT} (Note 5)	2	8	16	μs
Reverse Blocking Response Time	t _{RB}	Note 4		800		ns

Note 1: Stresses beyond the “Absolute Maximum Ratings” may cause permanent damage to the device. These are stress ratings only. Functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.







Note 2: θ_{JA} is measured in the natural convection at T_A = 25°C on the Silergy evaluation board. The exposed paddle of DFN2×2-6 packages is the case position for θ_{JC} measurement.







Note 3: The device is not guaranteed to function outside its operating conditions.

Note 4: Guaranteed by design but not production tested.

Note 5: The current limit threshold is determined by I_{LMT}=230V/R_{SET}, where R_{SET} is in Ω.


Typical Performance Characteristics





Short Circuit Response

($V_{IN}=5V$, $C_{IN}=C_{OUT}=10\mu F$)




Time (2μs/div)

Operation

The SY28892Z power switch integrates a P-channel MOSFET. It incorporates over-temperature protection and a current limiting function. Reverse blocking prevents current from flowing from OUT to IN when OUT is externally forced to a higher voltage than IN. The device is ideal for USB load-switching and hot-swap applications.

Application Schematic



BOM List

Reference Designator	Description	Part Number	Manufacturer
C ₁	10μF/10V, 0805	GRM21BR71A106KA73L+A01	Murata
C ₂	10μF/10V, 0805	GRM21BR71A106KA73L+A01	Murata
R ₁	1MΩ, 0603	RC0603FR-071ML	YAGEO
R ₂	100kΩ, 0603	RC0603FR-07100KL	YAGEO
R ₃	200Ω, 0603	RC0603FR-07200L	YAGEO

Over Current Protection

The SY28892Z supports current limit programming. Connect a resistor R_{SET} from the ISET pin to the ground to program the current limit:

$$I_{LIM} (A) = 230 / R_{SET} (\Omega)$$

The minimum current limit is 0.2A. A current limit beyond 2.0A is not recommended.

The internal current-limit amplifier regulates the output current to I_{LIM} for overload conditions. The output voltage will drop when the device operates in current regulation. If the over current condition persists for a long time, the junction temperature may exceed 150°C, and over-temperature protection will shut down the part. Once the temperature drops below 130°C, the part will automatically restart.

Table 1. Current Limit vs. R_{SET}

R _{SET} (Ω)	Current Limit Threshold(mA)		
	MIN	TYP	MAX
460.0	425	500	575
153.3	1380	1500	1620

During current limiting, the value will adjusted to around 60%×I_{LIM} to decrease power dissipation when V_{OUT}<50%×V_{IN}.

Fault Flag(OCB)

The OCB open-drain output is asserted (active low) when thermal shutdown protection is triggered or an over-current condition persists for 8μs. The OCB signal will remain asserted until the fault condition is removed. Connecting a heavy capacitance load to an enabled device can cause a momentary over-current condition. Connect OCB with a pull-up resistor to the IN or OUT voltage rail.

Supply Filter Capacitor

To prevent the input voltage drop during hot-plug events, a 10μF input ceramic bypass capacitor is recommended. However, higher capacitor values can further reduce the voltage drop on the input. Furthermore, shorting the output will generate a positive voltage spike on the input without the input capacitor. When such transients exceed the absolute maximum supply voltage, even for a short duration, it can damage the internal circuitry.

Output Filter Capacitor

A ceramic capacitor higher than 10μF is recommended. Place it close to the OUT pin to reduce the voltage drop during load transient. A larger value capacitor can further reduce the drop during high current applications.

Reverse Block Function

The SY28892Z integrates a reverse current blocking function. It monitors the reverse voltage from IN to OUT, and when it exceeds 100mV, it will shut down the power MOSFET in 700ns to stop the reverse current flow from OUT to IN.

PCB Layout Guide

For best performance of the SY28892Z, the following guidelines must be followed:

- High current carrying power path connections should be as short and wide as possible and use at least 2-ounce copper for all these traces.
- Place the output capacitor as close to the connectors as possible to lower the parasitic impedance (mainly inductance) between the port and the capacitor and improve transient performance.
- Place the input and output capacitors close to the device and connect to the ground plane to reduce noise coupling.






Figure 3. SY28892ZDEC PCB Layout Suggestion


DFN2x2-6 Package Outline




Top View



Side View



Bottom View




Recommended PCB Layout


Note: All dimensions are in millimeters and exclude mold flash and metal burr.

Taping & Reel Specification

DFN2x2 Taping Orientation



Carrier Tape & Reel Specification for Packages



Package types	Tape width (mm)	Pocket pitch(mm)	Reel size (Inch)	Trailer length(mm)	Leader length (mm)	Qty per reel
DFN2x2	8	4	7"	400	160	3000

Revision History

Date	Revision	Change
Aug.25, 2023	Revision 1.0	Language improvements for clarity
Nov.21, 2022	Revision 0.9A	Ambient Temperature Range changed from (-40°C to 85°C) to (-40°C to 105°C)
Nov.14, 2018	Revision 0.9	Initial Release

The revision history provided is for informational purposes only and is believed to be accurate; however, it is not warranted. Please make sure that you have the latest revision.

IMPORTANT NOTICE

1. **Right to make changes.** Silergy and its subsidiaries (hereafter Silergy) reserve the right to change any information published in this document, including but not limited to circuitry, specification and/or product design, manufacturing or descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to Silergy's standard terms and conditions of sale.

2. **Applications.** Application examples that are described herein for any of these products are for illustrative purposes only. Silergy makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Buyers are responsible for the design and operation of their applications and products using Silergy products. Silergy or its subsidiaries assume no liability for any application assistance or designs of customer products. It is customer's sole responsibility to determine whether the Silergy product is suitable and fit for the customer's applications and products planned. To minimize the risks associated with customer's products and applications, customer should provide adequate design and operating safeguards. Customer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Silergy assumes no liability related to any default, damage, costs or problem in the customer's applications or products, or the application or use by customer's third-party buyers. Customer will fully indemnify Silergy, its subsidiaries, and their representatives against any damages arising out of the use of any Silergy components in safety-critical applications. It is also buyers' sole responsibility to warrant and guarantee that any intellectual property rights of a third party are not infringed upon when integrating Silergy products into any application. Silergy assumes no responsibility for any said applications or for any use of any circuitry other than circuitry entirely embodied in a Silergy product.

3. **Limited warranty and liability.** Information furnished by Silergy in this document is believed to be accurate and reliable. However, Silergy makes no representation or warranty, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. In no event shall Silergy be liable for any indirect, incidental, punitive, special or consequential damages, including but not limited to lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges, whether or not such damages are based on tort or negligence, warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, Silergy's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Standard Terms and Conditions of Sale of Silergy.

4. **Suitability for use.** Customer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of Silergy components in its applications, notwithstanding any applications-related information or support that may be provided by Silergy. Silergy products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of a Silergy product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Silergy assumes no liability for inclusion and/or use of Silergy products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

5. **Terms and conditions of commercial sale.** Silergy products are sold subject to the standard terms and conditions of commercial sale, as published at <http://www.silergy.com/stdterms>, unless otherwise agreed in a valid written individual agreement specifically agreed to in writing by an authorized officer of Silergy. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Silergy hereby expressly objects to and denies the application of any customer's general terms and conditions with regard to the purchase of Silergy products by the customer.

6. **No offer to sell or license.** Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights. Silergy makes no representation or warranty that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right. Information published by Silergy regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from Silergy under the patents or other intellectual property of Silergy.

For more information, please visit: www.silergy.com

©2022 Silergy Corp.

All Rights Reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Silergy:](#)

[SY28892ZDEC](#)