

# StorFly® 18

1.8" SATA 6G SSD  
CE, XE, and PE Classes



## Industrial Embedded Technology for our Interconnected world

**StorFly 18 - Ideal for industrial  
automation, networking, server,  
blade and medical applications**

**Designed, built, and supported  
in the U.S. —fortified by locations  
worldwide**

## Overview

StorFly® 18 SATA CE, XE and PE SSDs deliver an optimal solid-state storage solution for embedded and industrial systems that may require a high-reliability replacement to hard-to-find 1.8" HDDs. StorFly 18 SSDs are also smaller, thinner, "eject-able" alternatives to 2.5".

SATA SSDs that provide the benefit of enhanced serviceability without the need for a hot-swap carrier. At a 5mm thickness, StorFly 18 SSDs are ideal for 1U server and blade applications where airflow and cooling are high priorities.

## Applications

StorFly 18 SSDs are ideal for industrial automation, networking, server, blade and medical applications that require high performance in a form factor only 5mm high. They are ideal as replacements for hard-to-find 1.8" HDDs and can be used in lieu of 2.5" for easy hot swapping and service.

StorFly 18 SSDs are also used in many military and ruggedized portable computers.

## Features

- Standard and industrial temperature
- vtGuard Power-Fail Protection
- vtView software accessible
- Global static and dynamic wear leveling

## Specifications

<b>Interface</b>	SATA 6G (SATA III), 3G and 1.5G
<b>Voltage / Power</b>	3.3v / 1.7W
<b>UBER</b>	<1 sector error in 1015 bits read
<b>MTBF</b>	> 2M hours
<b>Environmental</b>	MIL-STD-810F
<b>Compliance</b>	ATA/ATAPI-8 (ACS-2), FCC, CE, UL, RoHS, WEEE
<b>Dimensions (mm)</b>	54.00 x 78.25 x 5.0

Class			
<b>Media</b>	<b>MLC (Good)</b>	<b>iMLC (Better)</b>	<b>SLC (Best)</b>
<b>Capacity</b>	30GB-960GB	16GB-480GB	8GB-256GB
<b>*Endurance</b>	1X Baseline	7X Baseline	30X Baseline
<b>Operating Temperature</b>	0° to 70°C	-40° to 85°C	-40° to 85°C
<b>Warranty</b>	3 Years	5 Years	5 Years

\* Endurance Baseline = one entire drive write per day for the entire warranty period.

## Ordering Information

VSF18x(C/I)yyyG-zzz

where:

VSF	Virtium StorFly
B18x	Form factor and product class
(C/I)	Commercial / Industrial operating temp
yyyG	Capacity (1GB = 1,000,000,000 bytes)
zzz	Virtium proprietary

Virtium manufactures memory and storage solutions for the world's top industrial embedded OEMs. For two decades we have designed, built and supported our products in the USA - fortified by a network of global locations. Our world-class technology and unsurpassed support provide a superior customer experience that continuously results in better industrial embedded products for our increasingly interconnected world.

© Copyright 2018. All rights reserved. Virtium®, Storfly®, TuffDrive®, vtView®, vtGuard® are registered trademarks and vtSecure™ is a trademark of Virtium LLC. All other non-Virtium product names are trademarks of their respective companies.



30052 Tomas | Rancho Santa Margarita, CA 92688  
 Phone: 949-888-2444 | Fax: 949-888-2445  
[www.virtium.com](http://www.virtium.com)

PB001-1114-03

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Virtium:](#)

[VSFB18CC060G](#) [VSFB18PI128G](#) [VSFB18PC256G](#) [VSFB18XI480G](#) [VSFB18CC120G](#) [VSFB18XI030G](#)  
[VSFB18XI120G](#) [VSFB18XI060G](#) [VSFB18XI240G](#) [VSFB18PI032G](#) [VSFB18PI064G](#) [VSFB18PI256G](#)  
[VSFB18CC960G](#) [VSFB18CC480G](#) [VSFB18PC032G](#) [VSFB18PC128G](#) [VSFB18CC240G](#) [VSFB18PC064G](#)  
[VSFB18PI032G-110](#)