


CDBW46-G

Reverse Voltage: 100 Volts

Forward Current: 150 mA

RoHS Device




Features

- Design for mounting on small surface.
- High breakdown voltage.
- Low trun-on voltage.
- Guard ring construction for transient protection.

Mechanical data

- Case: SOD-123, Molded Plastic
- Terminals: Solderable per MIL-STD-202, Method 208
- Approx. Weight: 0.04 gram

Circuit diagram



Maximum Ratings (at Ta=25°C unless otherwise noted)

Parameter	Conditions	Symbol	Limits	Unit
Peak repetitive peak reverse voltage		V _{RRM}		
Working peak reverse voltage		V _{RWM}	100	V
DC blocking voltage		V _R		
Forward continuous current		I _F	150	mA
Repetitive Peak Forward current (Note 1)	@tp<1.0s, Duty Cycle<50%	I _{FRM}	350	mA
Forward surge Forward current (Note 1)	@tp<10ms	I _{FSM}	750	mA
Power dissipation		P _D	200	mW
Thermal Resistance Junction to ambient air		R _{θJA}	625	°C/W
Junction temperature		T _j	-55 to +150	°C
Storage temperature		T _{STG}	-55 to +150	°C

Electrical Characteristics (at Ta=25°C unless otherwise noted)

Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Reverse breakdown voltage (Note 2)	I _R =100μA	V _R	100			V
Forward voltage (Note 2)	I _{F1} = 0.1 mA I _{F2} = 10mA I _{F3} = 250mA	V _F			0.25 0.45 1.0	V
Reverse Voltage Leakage current	V _{R1} = 1.5V V _{R2} = 10V V _{R3} = 50V V _{R4} = 75V	I _R			0.3 0.5 1 2	μA
Diode capacitance	V _R =0V, f = 1 MHz V _R =1V, f = 1 MHz	C _T		20 12		pF

Notes: 1.Part mounted on FR-4 board with recommended pad layout.
2.Short duration pulse test used to minimize self-heating effect.

RATING AND CHARACTERISTIC CURVES (CDBW46-G)

Fig.1 - Typical Forward Characteristics




Fig.2 - Typical Reverse characteristics




Fig.3 - Total Capacitance vs. Reverse Voltage






Fig.4 - Forward Current Derating



Reel Taping Specification



SOD-123	SYMBOL	A	B	C	d	D	D1	D2
	(mm)	1.85 ± 0.10	3.94 ± 0.10	1.57 ± 0.10	1.55 ± 0.10	178 ± 1.00	54.40 ± 0.40	13.0 ± 0.20
	(inch)	0.073 ± 0.004	0.155 ± 0.004	0.062 ± 0.004	0.061 ± 0.004	7.008 ± 0.039	2.142 ± 0.016	0.512 ± 0.008

SOD-123	SYMBOL	E	F	P	P0	P1	W	W1
	(mm)	1.75 ± 0.10	3.50 ± 0.05	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.10	$8.00 \pm 0.30 / - 0.10$	9.50 ± 1.00
	(inch)	0.069 ± 0.004	0.138 ± 0.002	0.158 ± 0.004	0.158 ± 0.004	0.079 ± 0.004	$0.315 \pm 0.012 / - 0.004$	0.374 ± 0.039

Marking Code


Part Number	Marking Code
CDBW46-G	S9



xx= Product type marking code

Suggested PAD Layout

SIZE	SOD-123	
	(mm)	(inch)
A	3.35	0.132
B	0.80	0.031
C	1.00	0.039
D	4.15	0.163
E	2.55	0.100



Standard Packaging

Case Type	REEL PACK	
	REEL (pcs)	Reel Size (inch)
SOD-123	3,000	7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Comchip Technology:](#)

[CDBW46-G](#)