"US" Series

PCB-mount microsize, regulated, high-voltage DC-DC converter



Vin: 5Vdc, 12Vdc or 15Vdc

Vout: 0 to 200V, 300V, 400V or 500V

Pout: 100mW



MAKING HIGH VOLTAGE EASIER!®



At only 0.35in³ [5.75cc], the highly-compact microsize "US" Series is specially designed to meet the needs of professionals working to develop products for commercial, military, industrial and research applications. These units enable customers in domains including laser range finders, fiber-optic telecommunications and particle physics to achieve greater quantum efficiency and reduced total leakage current.

• miniature and lightweight

• option: flying wire for HV output

- PCB flat mounting
- inhibition mode
- tight line/load regulation
- output current limit protection
- temperature coefficient 50ppm/°C
- low ripple (<20mV p. to p.)
- low noise due to metal shielding
- 2.5V reference

| Parameters | Specifications | | |
|----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| Input voltage Vin (pins 1 & 2) | 5Vdc ± 0.5Vdc or 12 to 15Vdc ± 0.5Vdc according to type | | |
| | inhibition mode <5mA, at full output voltage, full load : | | |
| Input current | <65mA for the <60mA for the <55mA for the <50mA for the 200V model 300V model 400V model 500V model | | |
| HV output Vout (pin 7 or lead - optional) | programmable nominal voltage, refer to the Selection Guide for voltage ranges | | |
| Polarity | fixed positive or negative | | |
| HV setting (pins 3) | via external potentiometer, minimum resistance 10k Ω or via external voltage source 0/2.5V ±0.5% at full scale, and input impedance >1M Ω | | |
| Max. output current lout | refer to the Selection Guide | | |
| Load voltage regulation | ±0.01% of full output voltage for no load to full load | | |
| Line voltage regulation | ±0.01% of full output voltage over specified input voltage range | | |
| Residual ripple | less than 20mV peak-to-peak at full output voltage and current less than 5mV peak-to-peak at 200V and 200µA | | |
| Temperature coefficient | <50ppm/°C | | |
| Output HV monitoring (pin 2) | 0/2.5V signal accuracy : $\pm 0.2\%$ output impedance : $1 k\Omega$ | | |
| Output reference voltage (pin 4 - optional) | 2.5V ±0.5%, TC :50ppm/°C, max. output current : 1mA | | |
| HV power ON/OFF (pin 5) | ON : 0 volt, connected to ground OFF : not connected open collector compatible | | |
| Operating temperature | -10°C to +50°C | | |
| Storage temperature | -40°C to +70°C | | |
| Safeguards | output current internally limited soft start feature : start is guaranteed without overshoot | | |

Typical Applications


- Bias Supplies
- Avalanche Photo Diodes (APD)
- Silicon Photomultipliers (SiPM)

| Package Configuration | | | | |
|-----------------------|-------------------------------------------------------------|--|--|--|
| Case material | tin steel plate thickness 0.5mm | | | |
| Case dimensions LxHxW | 25.5 x 11.0 x 20.5 mm | | | |
| Pins | 0.63 x 0.63mm square pins, length : >2mm spacing : 2.54mm | | | |
| Weight | 13g | | | |
| Lead (optional) | coaxial cable (RG178), diameter = 2mm, length = 500mm | | | |
| Insulation | fully potted in an epoxy resin | | | |


| Pin Connections | | | | |
|-------------------|-----------------------------------|--|--|--|
| Line input : | 1.Vin | | | |
| - | 2.GND | | | |
| HV setting: | 3.control input | | | |
| | 4.output reference | | | |
| Inhibition input: | 5. ON/OFF | | | |
| HV monitoring: | Vout monitoring | | | |
| HV output : | 7.Vout | | | |



Mechanical Dimensions




seven pins: square 0.63x0.63 mm




six pins: square 0.63x0.63 mm option: flying wire for HV output

Functional Diagram



Ordering Information

| Model | name of the series | US |
|----------|--------------------------|-------------------|
| Vin | Vin 4.5Vdc to 5.5Vdc | |
| | 11.5Vdc to 15.5Vdc | 12 |
| Polarity | positive output voltage | -P |
| | negative output voltage | -N |
| Vout | output voltage | see Ordering Code |
| Pout | output power | see Ordering Code |
| Option | output voltage lead wire | -W |



+500V@100mW psu under 5Vdc with the flying wire for the HV output



"US" Series Selection Guide

| Vout | lout / Pout | Vin | Polarity | Model Number |
|--------------------|------------------|---------|----------|--------------|
| 500V 200μA / 100 | | 5V | + | 0.5US5-P0.1 |
| | 200uA / 100m\// | | - | 0.5US5-N0.1 |
| | 200μΑ/ 100111 | 12V-15V | + | 0.5US12-P0.1 |
| | | 120-130 | - | 0.5US12-N0.1 |
| 400V 250μA / 100mW | | 5V | + | 0.4US5-P0.1 |
| | 250µA / 100m\// | | - | 0.4US5-N0.1 |
| | 230μΑ/ 10011111 | 12V-15V | + | 0.4US12-P0.1 |
| | | | - | 0.4US12-N0.1 |
| 300V 330μA / 100mW | | 5V | + | 0.3US5-P0.1 |
| | 330uA / 100m\\\ | | - | 0.3US5-N0.1 |
| | 330μΑ/1001110 | 12V-15V | + | 0.3US12-P0.1 |
| | | | - | 0.3US12-N0.1 |
| 200V 500 | 500µA / 100mW | 5V | + | 0.2US5-P0.1 |
| | | | - | 0.2US5-N0.1 |
| | JooμA / Toollive | 12V-15V | + | 0.2US12-P0.1 |
| | | | - | 0.2US12-N0.1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Advanced Energy:

<u>0.2US5-P0.1</u> <u>0.4US12-P0.1</u> <u>0.2US12-N0.1</u> <u>0.5US5-N0.1</u> <u>0.3US5-N0.1</u> <u>0.3US5-P0.1</u> <u>0.2US12-P0.1</u> <u>0.2US12-P0.1</u> <u>0.2US5-N0.1</u> 0.4US12-N0.1 <u>0.3US12-P0.1</u> <u>0.5US12-P0.1</u> <u>0.5US12-P0.</u>