


GLOBAL PERFORMANCE SWITCHERS

FEATURES:

- Wide-range ac input 85-264 Vac
- 2-year warranty
- Conducted EMI complies with FCC Class B and CISPR 22 Class B (Commercial models) and CISPR 11 Class B (Medical models)
- Commercial Approved to UL1950, IEC950 and CSA22.2-234 L3
- Medical Approved to UL2601-1, IEC601-1 and CSA22.2 No. 601
- Complies with EN61000-3-2 Class A
- Single and multiple outputs
-  marked to LVD
- RoHS Compliant Model Available (G suffix)

CONDOR
DC Power Supplies



SPECIFICATIONS

Ac Input 85-264 Vac, 47-63 Hz single phase.	Output Noise 0.5% rms, 1% pk-pk, 20 MHz bandwidth, differential mode. Measured with noise probe directly across output terminals of the power supply.																
Input Current Maximum input current at 120 Vac, 60 Hz with full rated output load: 1.7 A	Transient Response Main output—500 μ s typical response time for return to within 0.5% of final value for a 50% load step change. $\Delta i/\Delta t < 0.2$ A/ μ s. Maximum voltage deviation is 3.5%. Startup/shutdown overshoot less than 3%.																
Hold-Up Time 20 ms minimum from loss of ac input at full load, nominal line (115 Vac).	Voltage Adjustment Built-in potentiometer adjusts voltage $\pm 5\%$ on outputs 1 & 2.																
Output Power 55 W continuous, 70 W peak. Peak ratings are for 60 s maximum duration, 10% duty cycle. During peak load condition, output regulation may exceed total regulation limits.	EMI/EMC Compliance All models include built-in EMI filtering to meet the following emissions requirements:																
Overload Protection Fully protected against short circuit and output overload. Short circuit protection is cycling type power limit on outputs 1 & 2; foldback type on outputs 3 & 4. Recovery after fault is automatic. See output ratings chart for additional notes or conditions. Factory set to begin power limiting at approximately 75 W.	<table> <thead> <tr> <th>EMI SPECIFICATIONS</th><th>COMPLIANCE LEVEL</th></tr> </thead> <tbody> <tr> <td>Conducted Emissions GPC55 Static</td><td>EN55022 Class B; FCC Class B</td></tr> <tr> <td>Conducted Emissions GPM55 Static</td><td>EN55011 Class B; FCC Class B</td></tr> <tr> <td>Static Discharge</td><td>EN61000-4-2, 6 kV contact, 8 kV air</td></tr> <tr> <td>RF Field Susceptibility</td><td>EN61000-4-3, 3 V/meter</td></tr> <tr> <td>Fast Transients/Bursts</td><td>EN61000-4-4, 2 kV, 5 kHz</td></tr> <tr> <td>Surge Susceptibility</td><td>EN61000-4-5, 1 kV diff., 2 kV com.</td></tr> <tr> <td>Line Frequency Harmonics</td><td>EN61000-3-2 Class A</td></tr> </tbody> </table>	EMI SPECIFICATIONS	COMPLIANCE LEVEL	Conducted Emissions GPC55 Static	EN55022 Class B; FCC Class B	Conducted Emissions GPM55 Static	EN55011 Class B; FCC Class B	Static Discharge	EN61000-4-2, 6 kV contact, 8 kV air	RF Field Susceptibility	EN61000-4-3, 3 V/meter	Fast Transients/Bursts	EN61000-4-4, 2 kV, 5 kHz	Surge Susceptibility	EN61000-4-5, 1 kV diff., 2 kV com.	Line Frequency Harmonics	EN61000-3-2 Class A
EMI SPECIFICATIONS	COMPLIANCE LEVEL																
Conducted Emissions GPC55 Static	EN55022 Class B; FCC Class B																
Conducted Emissions GPM55 Static	EN55011 Class B; FCC Class B																
Static Discharge	EN61000-4-2, 6 kV contact, 8 kV air																
RF Field Susceptibility	EN61000-4-3, 3 V/meter																
Fast Transients/Bursts	EN61000-4-4, 2 kV, 5 kHz																
Surge Susceptibility	EN61000-4-5, 1 kV diff., 2 kV com.																
Line Frequency Harmonics	EN61000-3-2 Class A																
Overvoltage Protection Main outputs: 124% + 12%	Commercial Leakage Current 0.7 mA 254 Vac @ 60 Hz input.																
Efficiency 70% at full rated load, nominal input voltage, depending on model and load distribution.	Commercial Safety Approved to UL1950, CSA22.2 No. 234 Level 3, IEC950 and EN60950. UL file #E135803 commercial; CSA #LR46516 all models. All dc outputs are SELV under normal and single fault conditions.																
Input Protection Internal ac fuse provided. Designed to blow only if a catastrophic failure occurs in the unit.	Medical Leakage Current 35 μ A 254 Vac @ 60 Hz input.																
Inrush Current Inrush is limited by internal thermistors. Inrush at 240 Vac under cold start conditions will not exceed 34 A.	Medical Safety Approved to UL2601, CSA22.2 No. 601 Level 3 and IEC601. UL file E116994; CSA #LR46516. The output(s) are intended for safety earthed Signal Output and Intermediate Circuits only. The output(s) are not acceptable for patient connection without additional isolation. All dc outputs are SELV under normal and single fault conditions.																
Temperature Coefficient 0.03%/°C typical on all outputs.																	
Environmental Designed for 0 to 50°C operation at full rated output power; derate output current and total output power by 2.5% per °C above 50°C. See Environmental and Packaging Specifications on next page.																	

Commercial Model	Medical Model	Output No.	Output	Output Minimum	Output Maximum	Output Peak	Noise P-P	Total Regulation (A)
GPC55A	GPM55A	1	+5 V	0.7 A	6 A	8 A	50 mV	2%
		2	+12 V	0 A	3 A	5 A	120 mV	2%
		3	+12 V	0 A	1 A	1.2 A	120 mV	3%
		4	-12 V	0 A	1 A	1.2 A	120 mV	3%
GPC55B	GPM55B	1	+5 V	0.7 A	6 A	8 A	50 mV	2%
		2	+12 V	0 A	3 A	5 A	120 mV	2%
		3	-5 V	0 A	1 A	1.2 A	50 mV	3%
		4	-12 V	0 A	1 A	1.2 A	120 mV	3%
GPC55C	GPM55C	1	+5 V	0.7 A	6 A	8 A	50 mV	2%
		2	+15 V	0 A	3 A	5 A	150 mV	2%
		3	-5 V	0 A	1 A	1.2 A	50 mV	3%
		4	-15 V	0 A	1 A	1.2 A	150 mV	3%
GPC55D	GPM55D	1	+5 V	0.7 A	6 A	8 A	50 mV	2%
		2	+24 V	0 A	1.5 A	5 A	240 mV	2%
		3	+12 V	0 A	1 A	1.2 A	120 mV	3%
		4	-12 V	0 A	1 A	1.2 A	120 mV	3%
GPC55E	GPM55E	1	+5 V	0.7 A	6 A	8 A	50 mV	2%
		2	+24 V	0 A	1.5 A	5 A	120 mV	2%
		3	+15 V	0 A	1 A	1.2 A	150 mV	3%
		4	-15 V	0 A	1 A	1.2 A	150 mV	3%
GPC55F	GPM55F	1	+5 V	0.7 A	6 A	8 A	50 mV	2%
		2	+12 V	0 A	3 A	5 A	120 mV	2%
		3	+15 V	0 A	1 A	1.2 A	150 mV	3%
		4	-15 V	0 A	1 A	11	150 mV	3%
GPC55-5	GPM55-5	1	5 V	0 A	11 A	14 A	50 mV	2%
GPC55-12	GPM55-12	1	12 V	0 A	4.7 A	5.8 A	120 mV	2%
GPC55-15	GPM55-15	1	15 V	0 A	3.7 A	4.7 A	150 mV	2%
GPC55-24	GPM55-24	1	24 V	0 A	2.3 A	2.9 A	240 mV	2%
GPC55-28	GPM55-28	1	28 V	0 A	2.0 A	2.4 A	280 mV	2%
GPC55-48		1	48 V	0 A	1.5 A	1.5 A	480 mV	2%

A. Total regulation is defined as the maximum deviation from the nominal voltage for all steady-state conditions of initial voltage setting, input line voltage and output load.
B. Add "G" suffix to model to indicate RoHS compliant model.

GPC55/GPM55 MECHANICAL SPECIFICATIONS


INPUT J1 AMP P/N 640445-5
0.156 [3.96mm] CTR HEADER
PIN 1) AC GROUND PIN 3) AC NEUTRAL PIN 5) AC LINE
PIN 2) N/C PIN 4) N/C

OUTPUT J2 AMP P/N 640445-9
0.156 [3.96mm] CTR HEADER

J2	MULTIPLE OUTPUT MODELS	SINGLE OUTPUT MODELS
PIN 1)	OUTPUT #2	OUTPUT #1
PIN 2)	OUTPUT #2	OUTPUT #1
PIN 3)	OUTPUT #1	OUTPUT #1
PIN 4)	OUTPUT #1	OUTPUT #1
PIN 5)	COMMON	COMMON
PIN 6)	COMMON	COMMON
PIN 7)	COMMON	COMMON
PIN 8)	OUTPUT #4	N/C
PIN 9)	OUTPUT #3	N/C

MATING CONNECTORS AMP P/N
HOUSING CONTACT
INPUT 640250-5 770476-1
OUTPUT 640250-9 770476-1

NOTE: 5A MAXIMUM RECOMMENDED CURRENT PER CONNECTOR PIN
OPTIONAL ENCLOSURE AVAILABLE, ORDER P/N 08-30486-1055
WEIGHT 1.5 LBS MAX. TOLERANCES: X,XX=0.030 [0.76mm]
[0.68 kg MAX.] X,XXX=0.010 [0.25mm]



ENVIRONMENTAL SPECIFICATIONS	OPERATING	NON-OPERATING
Temperature (A)	See individual Specs	-40 to +85°C
Humidity (A)	0 to 95% RH	0 to 95% RH
Shock (B)	20 g _{pk}	40 g _{pk}
Altitude	-500 to 10,000 ft	-500 to 40,000 ft
Vibration (C)	1.5 g _{rms} 0.003 g ² /Hz	5 g _{rms} 0.026 g ² /Hz

A. Units should be allowed to warm up/operate under non-condensing conditions before application of power.

B. Shock testing—half-sinusoidal, 10 ± 3 ms duration, ± direction, 3 orthogonal axes, total 6 shocks.

C. Random vibration—10 to 2000Hz, 6dB/octave roll-off from 350 to 2000Hz, 3 orthogonal axes. Tested for 10 min./axis operating and 1 hr./axis non-operating.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advanced Energy:](#)

[GPC55-5](#) [GPM55-24](#) [GPM55-28](#) [GPM55-12](#) [GPM55-15](#) [GPC55-15](#) [GPM55B](#) [GPM55D](#) [GPM55A](#) [GPM55E](#)
[GPM55C](#) [GPM55F](#) [GPC55D](#) [GPC55F](#) [GPC55E](#) [GPC55C](#) [GPC55-24](#) [GPC55B](#) [GPC55-48](#) [GPC55A](#) [GPM55-5](#)
[GPC55-12G](#) [GPC55-15G](#) [GPC55CG](#) [GPM55-5G](#) [GPC55-48G](#) [GPM55-24G](#) [GPM55-12G](#) [GPM55FG](#) [GPC55-5G](#)
[GPC55-24G](#) [GPC55-12](#) [GPC55-28](#) [GPC55-28G](#)